

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P205002

Luminaire Tested: **LSR6B30D010BZ EC6B30508030 6LBSCMMS1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P205002
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR6B30D010BZ EC6B30508030 6LBCSMMS1
Description: PORTFOLIO 6IN CYLINDER
SHALLOW DISTRIBUTION WITH CAST MATTE METALLIC SILVER TRIM
WATTAGE D010TR-27.4 W DE010-27.95 W D5LT-27.65 W DMX-27.73 W DL2-29.56 W
DL3-29.67 W DLE-29.73 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3039.3 lumens
Efficiency: N/A
Efficacy: 108.5 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.27
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P205002

CATALOG NUMBER: LSR6B30D010BZ EC6B30508030 6LBCSMMS1

Luminous Intensity Polar Plot





TEST NUMBER: P205002

CATALOG NUMBER: LSR6B30D010BZ EC6B30508030 6LBCSMMS1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	111	107	103	100	108	105	101	98	100	98	95	97	94	92	93	91	90	88																			
2	102	95	89	84	99	93	88	83	90	85	81	86	83	79	83	80	78	76																			
3	94	85	77	72	92	83	76	71	80	74	70	77	73	69	75	71	67	65																			
4	87	76	68	62	84	74	67	61	72	66	61	70	64	60	68	63	59	57																			
5	80	68	60	54	78	67	59	54	65	58	53	63	57	53	61	56	52	50																			
6	74	62	54	48	72	61	53	47	59	52	47	58	51	47	56	51	46	44																			
7	69	56	48	42	67	56	48	42	54	47	42	53	46	42	51	46	41	40																			
8	64	52	44	38	63	51	43	38	50	43	38	48	42	38	47	42	37	36																			
9	60	48	40	35	59	47	40	34	46	39	34	45	39	34	44	38	34	32																			
10	57	44	36	31	55	43	36	31	43	36	31	42	35	31	41	35	31	29																			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P205002

CATALOG NUMBER: LSR6B30D010BZ EC6B30508030 6LBCSMMS1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	131.5	4.3
10°-20°	369.1	12.1
20°-30°	539.1	17.7
30°-40°	616.6	20.3
40°-50°	592.6	19.5
50°-60°	457.6	15.1
60°-70°	255.4	8.4
70°-80°	74.3	2.4
80°-90°	3.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1039.7	34.2
0°-40°	1656.2	54.5
0°-60°	2706.4	89.0
0°-90°	3039.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3039.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1396	
5°	1384	132
15°	1309	369
25°	1172	539
35°	987	617
45°	772	593
55°	513	458
65°	256	255
75°	65	74
85°	2	3
90°	0	



TEST NUMBER: P205002

CATALOG NUMBER: LSR6B30D010BZ EC6B30508030 6LBCSMMS1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1395.7
2.5°	1395.7
5°	1383.9
7.5°	1378.0
10°	1358.4
12.5°	1334.8
15°	1309.2
17.5°	1283.7
20°	1246.3
22.5°	1216.8
25°	1171.6
27.5°	1126.4
30°	1081.2
32.5°	1036.0
35°	986.8
37.5°	937.7
40°	880.7
42.5°	829.6
45°	772.5
47.5°	707.7
50°	646.7
52.5°	579.9
55°	513.1
57.5°	444.3
60°	379.4
62.5°	314.5
65°	255.6
67.5°	200.5
70°	149.4
72.5°	104.2
75°	64.9
77.5°	33.4
80°	11.8
82.5°	3.9
85°	2.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)