

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P35132

Luminaire Tested: **LE_6B10D010 EC6B10209027 6LBNGPH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P35132
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B10D010 EC6B10209027 6LBNGPH1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
NARROW DISTRIBUTION WITH GRAPHITE HAZE TRIM
WATTAGE D010TR-10.05 W DE010-10.58 W D5LT-10.2 W DMX-10.6 W DL2-11.8 W
DL3-11.1 W DLE-11.39 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 548.1 lumens
Efficiency: N/A
Efficacy: 56.5 lumens/watt
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.88
Luminous Opening: Circular (Dia: 0.46' x H: 0')
CIE Type: Direct


Input Watts (W): 9.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P35132

CATALOG NUMBER: LE_6B10D010 EC6B10209027 6LBNGPH1

Luminous Intensity Polar Plot





TEST NUMBER: P35132

CATALOG NUMBER: LE_6B10D010 EC6B10209027 6LBNGPH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	108	106	111	109	106	104	105	103	101	101	100	98	97	96	95	94			
2	108	103	99	96	106	101	98	95	98	95	93	95	93	91	92	91	89	87			
3	103	96	91	87	101	95	90	87	92	88	85	90	87	84	88	85	83	81			
4	97	90	84	80	96	89	84	80	87	82	79	85	81	78	83	80	77	76			
5	93	84	78	74	91	83	78	74	82	77	73	80	76	73	78	75	72	70			
6	88	79	73	69	86	78	73	69	77	72	68	75	71	68	74	70	67	66			
7	84	74	68	64	82	74	68	64	72	67	64	71	67	63	70	66	63	62			
8	80	70	64	60	78	69	64	60	68	63	60	67	63	59	66	62	59	58			
9	76	66	60	56	75	66	60	56	65	60	56	64	59	56	63	59	56	54			
10	72	63	57	53	71	62	57	53	61	56	53	61	56	53	60	56	52	51			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	43463
5°	42405
10°	39669
15°	35966
20°	32110
25°	28348
30°	23918
35°	15626
40°	7878
45°	2879
50°	893
55°	569
60°	326
65°	185
70°	229
75°	0
80°	0
85°	0



TEST NUMBER: P35132

CATALOG NUMBER: LE_6B10D010 EC6B10209027 6LBNGPH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	60.3	11.0
10°-20°	148.7	27.1
20°-30°	180.2	32.9
30°-40°	122.8	22.4
40°-50°	29.2	5.3
50°-60°	4.6	0.8
60°-70°	1.7	0.3
70°-80°	0.5	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	389.3	71.0
0°-40°	512.1	93.4
0°-60°	545.9	99.6
0°-90°	548.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	548.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	666	
5°	648	60
15°	532	149
25°	394	180
35°	196	123
45°	31	29
55°	5	5
65°	1	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P35132

CATALOG NUMBER: LE_6B10D010 EC6B10209027 6LBNGPH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	666.2
2.5°	662.5
5°	647.5
7.5°	627.5
10°	598.8
12.5°	566.2
15°	532.5
17.5°	497.5
20°	462.5
22.5°	427.5
25°	393.8
27.5°	362.5
30°	317.5
32.5°	258.8
35°	196.2
37.5°	140.0
40°	92.5
42.5°	57.5
45°	31.2
47.5°	16.2
50°	8.8
52.5°	6.2
55°	5.0
57.5°	3.8
60°	2.5
62.5°	2.5
65°	1.2
67.5°	1.2
70°	1.2
72.5°	1.2
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)