

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P35138

Luminaire Tested: **LE_6B10D010 EC6B10209027 6LBSGPH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P35138
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B10D010 EC6B10209027 6LBSGPH1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH GRAPHITE HAZE TRIM
WATTAGE D010TR-10.05 W DE010-10.58 W D5LT-10.2 W DMX-10.6 W DL2-11.8 W
DL3-11.1 W DLE-11.39 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1041.6 lumens
Efficiency: N/A
Efficacy: 107.4 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.26
Luminous Opening: Circular (Dia: 0.46' x H: 0')
CIE Type: Direct


Input Watts (W): 9.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P35138

CATALOG NUMBER: LE_6B10D010 EC6B10209027 6LBSGPH1

Luminous Intensity Polar Plot





TEST NUMBER: P35138

CATALOG NUMBER: LE_6B10D010 EC6B10209027 6LBSGPH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	107	103	100	108	105	102	99	101	98	96	97	95	93	93	91	90	88			88
2	102	95	89	84	100	93	88	83	90	85	82	87	83	80	84	81	78	76			76
3	94	85	78	72	92	83	77	71	80	75	70	78	73	69	75	71	68	66			66
4	87	76	68	62	85	75	67	62	72	66	61	70	65	60	68	63	59	57			57
5	80	68	60	54	78	67	60	54	65	59	53	63	58	53	62	56	52	50			50
6	74	62	54	48	73	61	53	48	59	52	47	58	52	47	56	51	47	45			45
7	69	57	48	43	68	56	48	43	54	47	42	53	47	42	52	46	42	40			40
8	65	52	44	38	63	51	44	38	50	43	38	49	42	38	48	42	38	36			36
9	60	48	40	35	59	47	40	35	46	39	35	45	39	34	44	38	34	32			32
10	57	44	37	32	56	44	36	32	43	36	31	42	36	31	41	35	31	30			30

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	31563
5°	31435
10°	31216
15°	30651
20°	30027
25°	29154
30°	28160
35°	27079
40°	25976
45°	24450
50°	22451
55°	19905
60°	16806
65°	13307
70°	9309
75°	5041
80°	939
85°	0



TEST NUMBER: P35138

CATALOG NUMBER: LE_6B10D010 EC6B10209027 6LBSGPH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	45.5	4.4
10°-20°	127.9	12.3
20°-30°	186.5	17.9
30°-40°	212.6	20.4
40°-50°	204.0	19.6
50°-60°	156.2	15.0
60°-70°	85.7	8.2
70°-80°	22.8	2.2
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	359.9	34.6
0°-40°	572.5	55.0
0°-60°	932.7	89.5
0°-90°	1041.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1041.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	484	
5°	480	46
15°	454	128
25°	405	186
35°	340	213
45°	265	204
55°	175	156
65°	86	86
75°	20	23
85°	0	0
90°	0	



TEST NUMBER: P35138

CATALOG NUMBER: LE_6B10D010 EC6B10209027 6LBSGPH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	483.8
2.5°	482.5
5°	480.0
7.5°	476.2
10°	471.2
12.5°	462.5
15°	453.8
17.5°	443.8
20°	432.5
22.5°	418.8
25°	405.0
27.5°	391.2
30°	373.8
32.5°	357.5
35°	340.0
37.5°	322.5
40°	305.0
42.5°	286.2
45°	265.0
47.5°	243.8
50°	221.2
52.5°	197.5
55°	175.0
57.5°	152.5
60°	128.8
62.5°	106.2
65°	86.2
67.5°	66.2
70°	48.8
72.5°	32.5
75°	20.0
77.5°	8.8
80°	2.5
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)