

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204693

Luminaire Tested: **LSR6B30D010BZ EC6B30508030 6LBPSMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204693
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR6B30D010BZ EC6B30508030 6LBPSMW1
Description: PORTFOLIO 6IN CYLINDER
SHALLOW DISTRIBUTION WITH PLASTIC MATTE WHITE TRIM
WATTAGE D010TR-27.4 W DE010-27.95 W D5LT-27.65 W DMX-27.73 W DL2-29.56 W
DL3-29.67 W DLE-29.73 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3209.4 lumens
Efficiency: N/A
Efficacy: 114.6 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.34
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204693

CATALOG NUMBER: LSR6B30D010BZ EC6B30508030 6LBPSMW1

Luminous Intensity Polar Plot





TEST NUMBER: P204693

CATALOG NUMBER: LSR6B30D010BZ EC6B30508030 6LBPSMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	110	106	102	99	107	104	100	97	99	97	94	96	93	91	92	90	88	86			
2	101	93	87	82	98	92	86	81	88	83	79	85	81	77	82	79	76	74			
3	93	83	75	69	90	81	74	69	78	72	67	76	70	66	73	69	65	63			
4	85	74	66	59	83	72	65	59	70	63	58	68	62	57	66	61	56	54			
5	78	66	58	51	76	65	57	51	63	56	51	61	55	50	59	54	49	47			
6	73	60	51	45	71	59	51	45	57	50	44	55	49	44	54	48	44	42			
7	67	54	46	40	66	54	46	40	52	45	40	51	44	39	49	43	39	37			
8	63	50	41	36	61	49	41	36	48	41	35	46	40	35	45	39	35	33			
9	59	46	38	32	57	45	37	32	44	37	32	43	36	32	42	36	32	30			
10	55	42	34	29	54	42	34	29	41	34	29	40	33	29	39	33	29	27			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204693

CATALOG NUMBER: LSR6B30D010BZ EC6B30508030 6LBPSMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	122.5	3.8
10°-20°	349.3	10.9
20°-30°	526.0	16.4
30°-40°	625.9	19.5
40°-50°	624.7	19.5
50°-60°	508.1	15.8
60°-70°	312.6	9.7
70°-80°	121.1	3.8
80°-90°	19.4	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	997.8	31.1
0°-40°	1623.6	50.6
0°-60°	2756.4	85.9
0°-90°	3209.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3209.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1293	
5°	1289	123
15°	1240	349
25°	1145	526
35°	1002	626
45°	812	625
55°	569	508
65°	314	313
75°	110	121
85°	15	19
90°	0	



TEST NUMBER: P204693

CATALOG NUMBER: LSR6B30D010BZ EC6B30508030 6LBPSMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1293.1
2.5°	1295.0
5°	1289.3
7.5°	1281.7
10°	1272.2
12.5°	1255.1
15°	1239.9
17.5°	1217.0
20°	1192.3
22.5°	1169.5
25°	1144.8
27.5°	1110.5
30°	1076.3
32.5°	1044.0
35°	1002.2
37.5°	956.5
40°	914.7
42.5°	863.3
45°	812.0
47.5°	756.8
50°	697.9
52.5°	637.0
55°	568.6
57.5°	502.0
60°	437.4
62.5°	374.6
65°	313.8
67.5°	256.7
70°	203.5
72.5°	154.0
75°	110.3
77.5°	72.3
80°	43.7
82.5°	26.6
85°	15.2
87.5°	7.6
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)