

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P203255

Luminaire Tested: **LSR6B30D010BZ EC6B30509030 6LBMH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203255
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR6B30D010BZ EC6B30509030 6LBMH1
Description: PORTFOLIO 6IN CYLINDER
MEDIUM DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM
WATTAGE D010TR-27.4 W DE010-27.95 W D5LT-27.65 W DMX-27.73 W DL2-29.56 W
DL3-29.67 W DLE-29.73 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1844.7 lumens
Efficiency: N/A
Efficacy: 65.9 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.93
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203255

CATALOG NUMBER: LSR6B30D010BZ EC6B30509030 6LBMH1

Luminous Intensity Polar Plot





TEST NUMBER: P203255

CATALOG NUMBER: LSR6B30D010BZ EC6B30509030 6LBMH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	92		
2	107	102	97	93	105	100	96	92	97	93	90	94	91	88	91	89	87	85		
3	101	94	88	84	99	92	87	84	90	86	82	87	84	81	85	82	80	78		
4	95	87	81	76	93	86	80	76	84	79	75	82	78	74	80	76	73	72		
5	90	81	75	70	88	80	74	70	78	73	69	76	72	68	75	71	68	66		
6	85	75	69	64	83	75	69	64	73	68	64	72	67	63	70	66	63	61		
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57		
8	76	66	60	55	75	65	59	55	64	59	55	63	58	55	62	58	54	53		
9	72	62	56	51	71	61	55	51	60	55	51	60	55	51	59	54	51	49		
10	69	58	52	48	68	58	52	48	57	52	48	56	51	48	55	51	48	46		

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203255

CATALOG NUMBER: LSR6B30D010BZ EC6B30509030 6LBMH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	166.9	9.0
10°-20°	431.8	23.4
20°-30°	559.5	30.3
30°-40°	415.4	22.5
40°-50°	175.4	9.5
50°-60°	62.3	3.4
60°-70°	24.0	1.3
70°-80°	8.3	0.5
80°-90°	1.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1158.2	62.8
0°-40°	1573.6	85.3
0°-60°	1811.3	98.2
0°-90°	1844.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1844.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1826	
5°	1786	167
15°	1541	432
25°	1241	560
35°	659	415
45°	216	175
55°	66	62
65°	24	24
75°	8	8
85°	0	1
90°	0	



TEST NUMBER: P203255

CATALOG NUMBER: LSR6B30D010BZ EC6B30509030 6LBMH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1825.5
2.5°	1820.3
5°	1786.0
7.5°	1736.0
10°	1675.4
12.5°	1609.5
15°	1541.0
17.5°	1464.6
20°	1396.2
22.5°	1325.0
25°	1240.7
27.5°	1124.8
30°	987.8
32.5°	827.2
35°	658.6
37.5°	516.3
40°	392.5
42.5°	292.4
45°	216.0
47.5°	158.1
50°	115.9
52.5°	86.9
55°	65.9
57.5°	50.1
60°	39.5
62.5°	29.0
65°	23.7
67.5°	18.4
70°	13.2
72.5°	10.5
75°	7.9
77.5°	5.3
80°	2.6
82.5°	2.6
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)