

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P204974

Luminaire Tested: **LE\_6B10D010 EC6B10209727 6LBCS1MMS**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P204974  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LE\_6B10D010 EC6B10209727 6LBCS1MMS  
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT  
SHALLOW DISTRIBUTION WITH CAST MATTE METALLIC SILVER TRIM  
WATTAGE D010TR-10.05 W DE010-10.58 W D5LT-10.2 W DMX-10.6 W DL2-11.8 W  
DL3-11.1 W DLE-11.39 W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 975.9 lumens  
Efficiency: N/A  
Efficacy: 98.6 lumens/watt  
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.27  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 9.9  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P204974

CATALOG NUMBER: LE\_6B10D010 EC6B10209727 6LBCS1MMS

### Luminous Intensity Polar Plot





TEST NUMBER: P204974

CATALOG NUMBER: LE\_6B10D010 EC6B10209727 6LBCS1MMS

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	111	107	103	100	108	105	101	98	100	98	95	97	94	92	93	91	90	88			88																
2	102	95	89	84	99	93	88	83	90	85	81	86	83	79	83	80	78	76			76																
3	94	85	77	72	92	83	76	71	80	74	70	77	73	69	75	71	67	65			65																
4	87	76	68	62	84	74	67	61	72	66	61	70	64	60	68	63	59	57			57																
5	80	68	60	54	78	67	59	54	65	58	53	63	57	53	61	56	52	50			50																
6	74	62	54	48	72	61	53	47	59	52	47	58	51	47	56	51	46	44			44																
7	69	56	48	42	67	56	48	42	54	47	42	53	46	42	51	46	41	40			40																
8	64	52	44	38	63	51	43	38	50	43	38	48	42	38	47	42	37	36			36																
9	60	48	40	34	59	47	40	34	46	39	34	45	39	34	44	38	34	32			32																
10	57	44	36	31	55	43	36	31	43	36	31	42	35	31	41	35	31	29			29																

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P204974

CATALOG NUMBER: LE\_6B10D010 EC6B10209727 6LBCS1MMS

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	42.2	4.3
10°-20°	118.5	12.1
20°-30°	173.1	17.7
30°-40°	198.0	20.3
40°-50°	190.2	19.5
50°-60°	146.9	15.1
60°-70°	82.0	8.4
70°-80°	23.9	2.5
80°-90°	1.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	333.8	34.2
0°-40°	531.8	54.5
0°-60°	868.9	89.0
0°-90°	975.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	975.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	448	
5°	444	42
15°	420	118
25°	376	173
35°	317	198
45°	248	190
55°	165	147
65°	82	82
75°	21	24
85°	1	1
90°	0	



TEST NUMBER: P204974

CATALOG NUMBER: LE\_6B10D010 EC6B10209727 6LBCS1MMS

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	448.1
2.5°	448.1
5°	444.4
7.5°	442.5
10°	436.1
12.5°	428.6
15°	420.4
17.5°	412.1
20°	400.1
22.5°	390.8
25°	376.1
27.5°	361.6
30°	347.1
32.5°	332.6
35°	316.9
37.5°	301.1
40°	282.8
42.5°	266.4
45°	248.0
47.5°	227.2
50°	207.6
52.5°	186.2
55°	164.8
57.5°	142.6
60°	121.9
62.5°	101.0
65°	82.0
67.5°	64.4
70°	48.0
72.5°	33.5
75°	20.9
77.5°	10.8
80°	3.8
82.5°	1.2
85°	0.6
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)