

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P202637

Luminaire Tested: **LSR6B30D010BZ EC6B30509030 6LBMWMH1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P202637  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LSR6B30D010BZ EC6B30509030 6LBMWMH1  
Description: PORTFOLIO 6IN CYLINDER  
MEDIUM DISTRIBUTION WITH WARM HAZE TRIM  
WATTAGE D010TR-27.4 W DE010-27.95 W D5LT-27.65 W DMX-27.73 W DL2-29.56 W  
DL3-29.67 W DLE-29.73 W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1979.9 lumens  
Efficiency: N/A  
Efficacy: 70.7 lumens/watt  
Spacing Criteria (0/90/45): 0.9 / 0.9 / 0.89  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 28  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P202637

CATALOG NUMBER: LSR6B30D010BZ EC6B30509030 6LBMWMH1

### Luminous Intensity Polar Plot





TEST NUMBER: P202637

CATALOG NUMBER: LSR6B30D010BZ EC6B30509030 6LBMWMH1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |   |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|---|--|--|--|--|--|--|----|--|--|--|--|--|--|--|--|---|
| RF  | 20  |     |     |     |     |     |     |     |     | 20  |     |     |     |     |     |     |     |     | 20 |    |   |  |  |  |  |  |  | 20 |  |  |  |  |  |  |  |  |   |
| RC  | 80  |     |     |     |     |     |     |     |     | 50  |     |     |     |     |     |     |     |     | 30 |    |   |  |  |  |  |  |  | 10 |  |  |  |  |  |  |  |  | 0 |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30 | 10 | 0 |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |   |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 |    |    |   |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| 1   | 113 | 111 | 108 | 106 | 111 | 108 | 106 | 104 | 104 | 103 | 101 | 101 | 99  | 98  | 97  | 96  | 95  | 93  |    |    |   |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| 2   | 108 | 103 | 99  | 95  | 105 | 101 | 97  | 94  | 98  | 95  | 92  | 95  | 92  | 90  | 92  | 90  | 88  | 86  |    |    |   |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| 3   | 102 | 95  | 90  | 86  | 100 | 94  | 89  | 86  | 91  | 88  | 84  | 89  | 86  | 83  | 87  | 84  | 82  | 80  |    |    |   |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| 4   | 97  | 89  | 83  | 79  | 95  | 88  | 83  | 79  | 86  | 81  | 78  | 84  | 80  | 77  | 82  | 79  | 76  | 74  |    |    |   |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| 5   | 92  | 83  | 77  | 73  | 90  | 82  | 77  | 73  | 80  | 76  | 72  | 79  | 75  | 71  | 77  | 74  | 71  | 69  |    |    |   |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| 6   | 87  | 78  | 72  | 67  | 85  | 77  | 71  | 67  | 76  | 71  | 67  | 74  | 70  | 66  | 73  | 69  | 66  | 64  |    |    |   |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| 7   | 83  | 73  | 67  | 63  | 81  | 72  | 67  | 63  | 71  | 66  | 62  | 70  | 65  | 62  | 69  | 65  | 61  | 60  |    |    |   |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| 8   | 78  | 69  | 63  | 58  | 77  | 68  | 62  | 58  | 67  | 62  | 58  | 66  | 61  | 58  | 65  | 61  | 58  | 56  |    |    |   |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| 9   | 75  | 65  | 59  | 55  | 73  | 64  | 59  | 55  | 63  | 58  | 54  | 62  | 58  | 54  | 62  | 57  | 54  | 53  |    |    |   |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| 10  | 71  | 61  | 55  | 51  | 70  | 61  | 55  | 51  | 60  | 55  | 51  | 59  | 54  | 51  | 58  | 54  | 51  | 50  |    |    |   |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P202637

CATALOG NUMBER: LSR6B30D010BZ EC6B30509030 6LBMWMH1

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 202.1  | 10.2      |
| 10°-20°   | 518.8  | 26.2      |
| 20°-30°   | 637.2  | 32.2      |
| 30°-40°   | 436.9  | 22.1      |
| 40°-50°   | 140.4  | 7.1       |
| 50°-60°   | 28.5   | 1.4       |
| 60°-70°   | 11.2   | 0.6       |
| 70°-80°   | 4.2    | 0.2       |
| 80°-90°   | 0.7    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 1358.0 | 68.6      |
| 0°-40°    | 1794.9 | 90.7      |
| 0°-60°    | 1963.8 | 99.2      |
| 0°-90°    | 1979.9 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 1979.9 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 2202 |      |
| 5°  | 2160 | 202  |
| 15° | 1856 | 519  |
| 25° | 1406 | 637  |
| 35° | 697  | 437  |
| 45° | 166  | 140  |
| 55° | 29   | 28   |
| 65° | 12   | 11   |
| 75° | 3    | 4    |
| 85° | 0    | 1    |
| 90° | 0    |      |



TEST NUMBER: P202637

CATALOG NUMBER: LSR6B30D010BZ EC6B30509030 6LBMWMH1

**CANDELA DISTRIBUTION (FULL):**

| 0°    |        |
|-------|--------|
| 0°    | 2201.7 |
| 2.5°  | 2188.3 |
| 5°    | 2159.8 |
| 7.5°  | 2106.0 |
| 10°   | 2033.8 |
| 12.5° | 1944.8 |
| 15°   | 1855.8 |
| 17.5° | 1756.7 |
| 20°   | 1647.5 |
| 22.5° | 1533.3 |
| 25°   | 1405.7 |
| 27.5° | 1264.6 |
| 30°   | 1086.6 |
| 32.5° | 890.1  |
| 35°   | 697.0  |
| 37.5° | 520.6  |
| 40°   | 374.5  |
| 42.5° | 255.3  |
| 45°   | 166.3  |
| 47.5° | 102.4  |
| 50°   | 62.1   |
| 52.5° | 38.6   |
| 55°   | 28.6   |
| 57.5° | 21.8   |
| 60°   | 16.8   |
| 62.5° | 13.4   |
| 65°   | 11.8   |
| 67.5° | 8.4    |
| 70°   | 6.7    |
| 72.5° | 5.0    |
| 75°   | 3.4    |
| 77.5° | 3.4    |
| 80°   | 1.7    |
| 82.5° | 1.7    |
| 85°   | 0.0    |
| 87.5° | 0.0    |
| 90°   | 0.0    |



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)