

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P203117

Luminaire Tested: **LE\_6B10D010 EC6B10209727 6LBWMW1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P203117  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LE\_6B10D010 EC6B10209727 6LBWMW1  
Description: PORTFOLIO 6 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT  
WIDE DISTRIBUTION WITH MATTE WHITE TRIM  
WATTAGE D010TR-10.05 W DE010-10.58 W D5LT-10.2 W DMX-10.6 W DL2-11.8 W  
DL3-11.1 W DLE-11.39 W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 896.9 lumens  
Efficiency: N/A  
Efficacy: 90.6 lumens/watt  
Spacing Criteria (0/90/45): 1.13 / 1.13 / 1.15  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct

Input Watts (W): 9.9  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P203117  
CATALOG NUMBER: LE\_6B10D010 EC6B10209727 6LBWMW1

### Luminous Intensity Polar Plot





TEST NUMBER: P203117

CATALOG NUMBER: LE\_6B10D010 EC6B10209727 6LBWMW1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	111	107	104	100	108	105	102	99	101	98	96	97	95	93	93	92	90	88	88	88	88
2	103	96	90	86	100	94	89	85	91	86	83	88	84	81	85	82	79	77	77	77	77
3	95	86	80	74	93	85	79	74	82	77	72	80	75	71	77	73	70	68	68	68	68
4	89	78	71	65	86	77	70	65	75	69	64	72	67	63	70	66	62	60	60	60	60
5	82	71	64	58	80	70	63	58	68	62	57	66	61	56	65	60	56	54	54	54	54
6	77	65	57	52	75	64	57	52	63	56	51	61	55	51	60	54	50	49	49	49	49
7	72	60	52	47	70	59	52	47	58	51	46	56	50	46	55	50	46	44	44	44	44
8	67	55	48	42	66	55	47	42	53	47	42	52	46	42	51	46	42	40	40	40	40
9	63	51	44	39	62	51	44	39	50	43	39	49	43	38	48	42	38	37	37	37	37
10	60	48	40	36	58	47	40	36	46	40	36	45	40	35	45	39	35	34	34	34	34

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P203117

CATALOG NUMBER: LE\_6B10D010 EC6B10209727 6LBWMW1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	47.4	5.3
10°-20°	133.0	14.8
20°-30°	191.7	21.4
30°-40°	199.0	22.2
40°-50°	147.1	16.4
50°-60°	87.9	9.8
60°-70°	53.4	6.0
70°-80°	29.3	3.3
80°-90°	8.1	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	372.1	41.5
0°-40°	571.1	63.7
0°-60°	806.1	89.9
0°-90°	896.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	896.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	504	
5°	500	47
15°	472	133
25°	418	192
35°	321	199
45°	189	147
55°	96	88
65°	53	53
75°	27	29
85°	6	8
90°	0	



TEST NUMBER: P203117

CATALOG NUMBER: LE\_6B10D010 EC6B10209727 6LBWMW1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	503.6
2.5°	503.6
5°	500.4
7.5°	496.0
10°	489.5
12.5°	481.9
15°	472.1
17.5°	461.2
20°	450.4
22.5°	435.1
25°	417.8
27.5°	399.2
30°	375.2
32.5°	351.4
35°	320.9
37.5°	289.4
40°	254.5
42.5°	220.8
45°	189.2
47.5°	161.0
50°	136.0
52.5°	114.2
55°	95.8
57.5°	81.6
60°	69.6
62.5°	60.9
65°	53.2
67.5°	46.8
70°	40.2
72.5°	33.8
75°	27.2
77.5°	21.8
80°	16.4
82.5°	12.0
85°	6.5
87.5°	3.2
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)