

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P203569

Luminaire Tested: **LSR6B30D010BZ EC6B30509730 6LBMMW1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P203569  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LSR6B30D010BZ EC6B30509730 6LBMMW1  
Description: PORTFOLIO 6IN CYLINDER  
MEDIUM DISTRIBUTION WITH MATTE WHITE TRIM  
WATTAGE D010TR-27.4 W DE010-27.95 W D5LT-27.65 W DMX-27.73 W DL2-29.56 W  
DL3-29.67 W DLE-29.73 W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1769.2 lumens  
Efficiency: N/A  
Efficacy: 63.2 lumens/watt  
Spacing Criteria (0/90/45): 1 / 1 / 0.97  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 28  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P203569

CATALOG NUMBER: LSR6B30D010BZ EC6B30509730 6LBMMW1

### Luminous Intensity Polar Plot





TEST NUMBER: P203569

CATALOG NUMBER: LSR6B30D010BZ EC6B30509730 6LBMMW1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	108	104	101	109	105	103	100	101	99	97	98	96	94	94	92	91	89			
2	104	97	92	88	101	96	91	87	92	88	85	89	86	83	86	83	81	79			
3	97	88	82	77	95	87	81	76	84	79	75	82	77	74	79	76	73	71			
4	90	81	74	68	88	80	73	68	77	72	67	75	70	66	73	69	65	64			
5	85	74	67	61	83	73	66	61	71	65	61	69	64	60	68	63	59	58			
6	79	68	61	56	78	68	61	56	66	60	55	64	59	55	63	58	54	53			
7	75	63	56	51	73	63	56	51	61	55	50	60	54	50	59	54	50	48			
8	70	59	52	47	69	58	51	47	57	51	46	56	50	46	55	50	46	44			
9	66	55	48	43	65	54	48	43	53	47	43	52	47	43	51	46	43	41			
10	63	51	45	40	62	51	44	40	50	44	40	49	44	40	48	43	40	38			

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P203569

CATALOG NUMBER: LSR6B30D010BZ EC6B30509730 6LBMMW1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	121.9	6.9
10°-20°	326.6	18.5
20°-30°	438.6	24.8
30°-40°	359.8	20.3
40°-50°	216.0	12.2
50°-60°	143.6	8.1
60°-70°	96.2	5.4
70°-80°	51.8	2.9
80°-90°	14.6	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	887.2	50.1
0°-40°	1246.9	70.5
0°-60°	1606.5	90.8
0°-90°	1769.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1769.2	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1320	
5°	1298	122
15°	1164	327
25°	966	439
35°	571	360
45°	273	216
55°	159	144
65°	98	96
75°	49	52
85°	12	15
90°	0	



TEST NUMBER: P203569

CATALOG NUMBER: LSR6B30D010BZ EC6B30509730 6LBMMW1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1320.1
2.5°	1310.3
5°	1298.1
7.5°	1271.3
10°	1239.5
12.5°	1200.5
15°	1163.9
17.5°	1120.0
20°	1076.1
22.5°	1027.3
25°	966.3
27.5°	893.1
30°	795.5
32.5°	685.7
35°	571.0
37.5°	473.4
40°	390.4
42.5°	324.5
45°	273.3
47.5°	231.8
50°	202.5
52.5°	178.1
55°	158.6
57.5°	141.5
60°	126.9
62.5°	109.8
65°	97.6
67.5°	83.0
70°	70.8
72.5°	58.6
75°	48.8
77.5°	39.0
80°	29.3
82.5°	22.0
85°	12.2
87.5°	4.9
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)