

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P202490

Luminaire Tested: **LE\_6B10D010 EC6B10208030 6LBSWMH1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P202490  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LE\_6B10D010 EC6B10208030 6LBSWMH1  
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT  
SHALLOW DISTRIBUTION WITH WARM HAZE TRIM  
WATTAGE D010TR-10.05 W DE010-10.58 W D5LT-10.2 W DMX-10.6 W DL2-11.8 W  
DL3-11.1 W DLE-11.39 W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1396.5 lumens  
Efficiency: N/A  
Efficacy: 141.1 lumens/watt  
Spacing Criteria (0/90/45): 0.97 / 0.97 / 1.1  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 9.9  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P202490

CATALOG NUMBER: LE\_6B10D010 EC6B10208030 6LBSWMH1

### Luminous Intensity Polar Plot





TEST NUMBER: P202490

CATALOG NUMBER: LE\_6B10D010 EC6B10208030 6LBSWMH1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	94	92	90	88				88
2	103	96	90	85	100	94	89	84	91	86	82	87	84	81	84	81	79	77				77
3	95	86	79	73	92	84	78	73	81	76	71	79	74	70	76	72	69	67				67
4	88	77	70	64	86	76	69	63	74	67	62	71	66	62	69	65	61	59				59
5	81	70	62	56	79	69	61	56	67	60	55	65	59	55	63	58	54	52				52
6	76	64	56	50	74	63	55	50	61	54	49	59	53	49	58	53	48	47				47
7	70	58	50	45	69	57	50	45	56	49	44	55	48	44	53	48	44	42				42
8	66	54	46	40	64	53	45	40	52	45	40	50	44	40	49	44	40	38				38
9	62	49	42	37	61	49	42	37	48	41	37	47	41	36	46	40	36	35				35
10	58	46	39	34	57	45	38	34	45	38	34	44	38	33	43	37	33	32				32

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P202490

CATALOG NUMBER: LE\_6B10D010 EC6B10208030 6LBSWMH1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	74.7	5.3
10°-20°	195.3	14.0
20°-30°	259.0	18.5
30°-40°	276.2	19.8
40°-50°	258.2	18.5
50°-60°	196.9	14.1
60°-70°	107.1	7.7
70°-80°	28.7	2.1
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	529.0	37.9
0°-40°	805.2	57.7
0°-60°	1260.3	90.2
0°-90°	1396.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1396.5	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	808	
5°	796	75
15°	696	195
25°	564	259
35°	441	276
45°	336	258
55°	222	197
65°	107	107
75°	25	29
85°	0	0
90°	0	



TEST NUMBER: P202490

CATALOG NUMBER: LE\_6B10D010 EC6B10208030 6LBSWMH1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	807.5
2.5°	804.9
5°	796.4
7.5°	778.4
10°	757.9
12.5°	728.8
15°	696.2
17.5°	663.8
20°	628.8
22.5°	595.4
25°	563.8
27.5°	530.4
30°	498.8
32.5°	467.9
35°	441.4
37.5°	414.9
40°	387.5
42.5°	362.6
45°	336.1
47.5°	307.1
50°	279.8
52.5°	250.6
55°	221.5
57.5°	189.9
60°	160.9
62.5°	133.5
65°	106.9
67.5°	83.0
70°	60.8
72.5°	41.9
75°	24.8
77.5°	11.1
80°	2.6
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)