

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204496

Luminaire Tested: **LSR6B30D010BZ EC6B30509730 6LBSB1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204496
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR6B30D010BZ EC6B30509730 6LBSB1
Description: PORTFOLIO 6IN CYLINDER
SHALLOW DISTRIBUTION WITH SPECULAR BLACK TRIM
WATTAGE D010TR-27.4 W DE010-27.95 W D5LT-27.65 W DMX-27.73 W DL2-29.56 W
DL3-29.67 W DLE-29.73 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2019.4 lumens
Efficiency: N/A
Efficacy: 72.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.2 / 1.3
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204496

CATALOG NUMBER: LSR6B30D010BZ EC6B30509730 6LBSB1

Luminous Intensity Polar Plot





TEST NUMBER: P204496

CATALOG NUMBER: LSR6B30D010BZ EC6B30509730 6LBSB1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	107	103	100	108	105	101	98	100	98	95	97	94	93	93	91	90	88			88
2	102	95	89	84	100	93	88	83	90	85	81	86	83	79	84	80	78	76			76
3	94	84	77	72	91	83	76	71	80	74	70	77	73	68	75	71	67	65			65
4	86	76	68	62	84	74	67	61	72	65	60	70	64	60	68	63	59	57			57
5	80	68	60	54	78	67	59	53	65	58	53	63	57	52	61	56	52	50			50
6	74	62	53	47	72	61	53	47	59	52	47	57	51	46	56	50	46	44			44
7	69	56	48	42	67	55	48	42	54	47	42	52	46	41	51	45	41	39			39
8	64	51	43	38	63	51	43	38	49	42	37	48	42	37	47	41	37	35			35
9	60	47	39	34	59	47	39	34	46	39	34	45	38	34	44	38	34	32			32
10	56	44	36	31	55	43	36	31	42	36	31	41	35	31	40	35	31	29			29

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204496

CATALOG NUMBER: LSR6B30D010BZ EC6B30509730 6LBSB1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	84.1	4.2
10°-20°	238.6	11.8
20°-30°	354.9	17.6
30°-40°	412.9	20.4
40°-50°	402.5	19.9
50°-60°	309.6	15.3
60°-70°	171.2	8.5
70°-80°	45.3	2.2
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	677.5	33.5
0°-40°	1090.4	54.0
0°-60°	1802.5	89.3
0°-90°	2019.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2019.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	891	
5°	886	84
15°	845	239
25°	770	355
35°	663	413
45°	522	403
55°	346	310
65°	172	171
75°	38	45
85°	0	0
90°	0	



TEST NUMBER: P204496

CATALOG NUMBER: LSR6B30D010BZ EC6B30509730 6LBSB1

CANDELA DISTRIBUTION (FULL):

	0°
0°	890.8
2.5°	890.8
5°	885.7
7.5°	878.0
10°	872.9
12.5°	857.5
15°	844.7
17.5°	831.9
20°	814.0
22.5°	796.1
25°	770.5
27.5°	744.9
30°	719.3
32.5°	691.1
35°	663.0
37.5°	627.1
40°	596.4
42.5°	563.2
45°	522.2
47.5°	483.8
50°	440.3
52.5°	394.2
55°	345.6
57.5°	299.5
60°	256.0
62.5°	212.5
65°	171.5
67.5°	133.1
70°	97.3
72.5°	66.6
75°	38.4
77.5°	17.9
80°	2.6
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)