

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P205172

Luminaire Tested: **LE\_6B10D010 EC6B10209030 6LBWLI1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P205172  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LE\_6B10D010 EC6B10209030 6LBWL1  
Description: PORTFOLIO 6 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT  
WIDE DISTRIBUTION WITH SPECULAR CLEAR TRIM  
WATTAGE D010TR-10.05 W DE010-10.58 W D5LT-10.2 W DMX-10.6 W DL2-11.8 W  
DL3-11.1 W DLE-11.39 W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1146.7 lumens  
Efficiency: N/A  
Efficacy: 115.8 lumens/watt  
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.18  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 9.9  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P205172

CATALOG NUMBER: LE\_6B10D010 EC6B10209030 6LBWLI1

### Luminous Intensity Polar Plot





TEST NUMBER: P205172

CATALOG NUMBER: LE\_6B10D010 EC6B10209030 6LBWLI1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	110	107	104	110	107	105	103	103	101	99	100	98	97	96	95	94	92				92
2	106	101	96	92	104	99	95	91	95	92	89	92	90	87	90	87	85	83				83
3	100	92	87	82	97	91	86	81	88	84	80	86	82	79	83	80	77	76				76
4	93	85	78	74	92	84	78	73	81	76	72	79	75	71	77	74	70	69				69
5	88	78	71	66	86	77	71	66	75	70	65	73	69	65	72	68	64	63				63
6	82	72	65	60	81	71	65	60	70	64	59	68	63	59	67	62	59	57				57
7	77	67	60	55	76	66	59	55	65	59	54	63	58	54	62	57	54	52				52
8	73	62	55	50	71	61	55	50	60	54	50	59	54	50	58	53	49	48				48
9	69	57	51	46	67	57	50	46	56	50	46	55	50	46	54	49	46	44				44
10	65	54	47	43	64	53	47	43	52	46	42	51	46	42	51	46	42	41				41

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P205172

CATALOG NUMBER: LE\_6B10D010 EC6B10209030 6LBWLI1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	69.1	6.0
10°-20°	207.7	18.1
20°-30°	313.1	27.3
30°-40°	320.5	27.9
40°-50°	186.7	16.3
50°-60°	42.9	3.7
60°-70°	5.3	0.5
70°-80°	1.3	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	590.0	51.4
0°-40°	910.4	79.4
0°-60°	1140.1	99.4
0°-90°	1146.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1146.7	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	716	
5°	720	69
15°	736	208
25°	686	313
35°	520	320
45°	240	187
55°	42	43
65°	4	5
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P205172

CATALOG NUMBER: LE\_6B10D010 EC6B10209030 6LBWLI1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	716.4
2.5°	715.1
5°	720.2
7.5°	725.5
10°	732.0
12.5°	733.2
15°	735.9
17.5°	733.2
20°	726.8
22.5°	706.0
25°	686.5
27.5°	655.2
30°	615.0
32.5°	573.4
35°	520.0
37.5°	460.2
40°	394.0
42.5°	319.9
45°	240.5
47.5°	167.8
50°	110.5
52.5°	70.2
55°	41.6
57.5°	22.1
60°	11.8
62.5°	6.5
65°	3.9
67.5°	3.9
70°	2.6
72.5°	1.2
75°	1.2
77.5°	1.2
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)