

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P203868

Luminaire Tested: **LSR6B30D010BZ EC6B30508035 6LBNGPH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203868
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR6B30D010BZ EC6B30508035 6LBNGPH1
Description: PORTFOLIO 6IN CYLINDER
NARROW DISTRIBUTION WITH GRAPHITE HAZE TRIM
WATTAGE D010TR-27.4 W DE010-27.95 W D5LT-27.65 W DMX-27.73 W DL2-29.56 W
DL3-29.67 W DLE-29.73 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1523.1 lumens
Efficiency: N/A
Efficacy: 54.4 lumens/watt
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.88
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203868

CATALOG NUMBER: LSR6B30D010BZ EC6B30508035 6LBNGPH1

Luminous Intensity Polar Plot





TEST NUMBER: P203868

CATALOG NUMBER: LSR6B30D010BZ EC6B30508035 6LBNGPH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	108	106	111	109	106	104	105	103	101	101	100	98	97	96	95	94
2	108	103	99	96	106	101	98	95	98	95	93	95	93	91	92	91	89	87
3	103	96	91	87	101	95	90	87	92	88	85	90	87	84	88	85	83	81
4	97	90	84	80	96	89	84	80	87	82	79	85	81	78	83	80	77	76
5	93	84	78	74	91	83	78	74	82	77	73	80	76	73	78	75	72	70
6	88	79	73	69	86	78	73	69	77	72	68	75	71	68	74	70	67	66
7	84	74	68	64	82	74	68	64	72	67	64	71	67	63	70	66	63	62
8	79	70	64	60	78	69	64	60	68	63	60	67	63	59	66	62	59	58
9	76	66	60	56	75	66	60	56	65	60	56	64	59	56	63	59	56	54
10	72	63	57	53	71	62	57	53	61	56	53	61	56	53	60	55	52	51

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203868

CATALOG NUMBER: LSR6B30D010BZ EC6B30508035 6LBNGPH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	167.6	11.0
10°-20°	413.3	27.1
20°-30°	500.8	32.9
30°-40°	341.3	22.4
40°-50°	81.3	5.3
50°-60°	12.7	0.8
60°-70°	4.7	0.3
70°-80°	1.4	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1081.7	71.0
0°-40°	1423.0	93.4
0°-60°	1517.0	99.6
0°-90°	1523.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1523.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1851	
5°	1799	168
15°	1480	413
25°	1094	501
35°	545	341
45°	87	81
55°	14	13
65°	4	5
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P203868

CATALOG NUMBER: LSR6B30D010BZ EC6B30508035 6LBNGPH1

CANDELA DISTRIBUTION (FULL):

0°	
0°	1851.3
2.5°	1840.9
5°	1799.2
7.5°	1743.7
10°	1663.8
12.5°	1573.5
15°	1479.7
17.5°	1382.4
20°	1285.2
22.5°	1187.9
25°	1094.1
27.5°	1007.3
30°	882.2
32.5°	719.0
35°	545.3
37.5°	389.0
40°	257.0
42.5°	159.8
45°	86.8
47.5°	45.2
50°	24.3
52.5°	17.4
55°	13.9
57.5°	10.4
60°	6.9
62.5°	6.9
65°	3.5
67.5°	3.5
70°	3.5
72.5°	3.5
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)