

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P204251

Luminaire Tested: **LE\_6B10D010 EC6B10209730 6LBSWH1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P204251  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LE\_6B10D010 EC6B10209730 6LBSWH1  
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT  
SHALLOW DISTRIBUTION WITH WHEAT TRIM  
WATTAGE D010TR-10.05 W DE010-10.58 W D5LT-10.2 W DMX-10.6 W DL2-11.8 W  
DL3-11.1 W DLE-11.39 W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1038.3 lumens  
Efficiency: N/A  
Efficacy: 104.9 lumens/watt  
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1.08  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 9.9  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P204251

CATALOG NUMBER: LE\_6B10D010 EC6B10209730 6LBSWH1

### Luminous Intensity Polar Plot





TEST NUMBER: P204251

CATALOG NUMBER: LE\_6B10D010 EC6B10209730 6LBSWH1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	94	92	90	89																			
2	103	96	90	85	100	94	89	85	91	86	83	87	84	81	85	82	79	77																			
3	95	86	79	73	93	84	78	73	82	76	72	79	74	70	76	73	69	67																			
4	88	77	70	64	86	76	69	63	74	68	63	72	66	62	69	65	61	59																			
5	81	70	62	56	79	69	62	56	67	60	55	65	59	55	63	58	54	52																			
6	76	64	56	50	74	63	55	50	61	54	49	60	54	49	58	53	49	47																			
7	71	58	51	45	69	58	50	45	56	49	45	55	49	44	54	48	44	42																			
8	66	54	46	41	65	53	46	41	52	45	40	51	45	40	50	44	40	38																			
9	62	50	42	37	61	49	42	37	48	41	37	47	41	37	46	41	37	35																			
10	58	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32																			

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P204251

CATALOG NUMBER: LE\_6B10D010 EC6B10209730 6LBSWH1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	57.1	5.5
10°-20°	147.8	14.2
20°-30°	193.3	18.6
30°-40°	204.8	19.7
40°-50°	191.0	18.4
50°-60°	144.6	13.9
60°-70°	78.4	7.5
70°-80°	21.0	2.0
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	398.3	38.4
0°-40°	603.1	58.1
0°-60°	938.7	90.4
0°-90°	1038.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1038.3	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	619	
5°	610	57
15°	528	148
25°	420	193
35°	327	205
45°	249	191
55°	162	145
65°	78	78
75°	18	21
85°	0	0
90°	0	



TEST NUMBER: P204251

CATALOG NUMBER: LE\_6B10D010 EC6B10209730 6LBSWH1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	619.2
2.5°	617.0
5°	610.1
7.5°	595.4
10°	576.1
12.5°	553.4
15°	528.4
17.5°	500.0
20°	475.0
22.5°	446.5
25°	420.4
27.5°	394.2
30°	369.2
32.5°	347.8
35°	327.2
37.5°	306.8
40°	287.5
42.5°	268.1
45°	248.9
47.5°	227.2
50°	205.6
52.5°	184.1
55°	162.5
57.5°	139.8
60°	118.1
62.5°	97.8
65°	78.4
67.5°	60.2
70°	44.4
72.5°	30.6
75°	18.1
77.5°	8.0
80°	2.2
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)