

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204075

Luminaire Tested: **LSR6B30D010BZ EC6B30508040 6LBNMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204075
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR6B30D010BZ EC6B30508040 6LBNMW1
Description: PORTFOLIO 6IN CYLINDER
NARROW DISTRIBUTION WITH MATTE WHITE TRIM
WATTAGE D010TR-27.4 W DE010-27.95 W D5LT-27.65 W DMX-27.73 W DL2-29.56 W
DL3-29.67 W DLE-29.73 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2209.3 lumens
Efficiency: N/A
Efficacy: 78.9 lumens/watt
Spacing Criteria (0/90/45): 0.99 / 0.99 / 0.97
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204075

CATALOG NUMBER: LSR6B30D010BZ EC6B30508040 6LBNMW1

Luminous Intensity Polar Plot





TEST NUMBER: P204075

CATALOG NUMBER: LSR6B30D010BZ EC6B30508040 6LBNMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20																	
RC	80									70									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																								
RCR																																																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																																				
1	112	108	105	103	109	106	103	101	102	100	98	98	97	95	95	93	92	90																																				
2	105	99	94	90	102	97	92	89	94	90	87	91	87	85	88	85	83	81																																				
3	98	90	84	79	96	89	83	79	86	81	77	84	80	76	81	78	75	73																																				
4	92	83	76	71	90	82	76	71	80	74	70	77	73	69	75	71	68	66																																				
5	87	77	70	65	85	76	69	64	74	68	64	72	67	63	70	66	62	61																																				
6	81	71	64	59	80	70	63	59	68	63	58	67	62	58	66	61	57	56																																				
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51																																				
8	72	61	55	50	71	61	54	50	60	54	49	59	53	49	58	53	49	47																																				
9	69	58	51	46	67	57	51	46	56	50	46	55	50	46	54	49	46	44																																				
10	65	54	47	43	64	54	47	43	53	47	43	52	46	43	51	46	43	41																																				

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204075

CATALOG NUMBER: LSR6B30D010BZ EC6B30508040 6LBNMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	168.2	7.6
10°-20°	446.0	20.2
20°-30°	595.4	27.0
30°-40°	480.4	21.7
40°-50°	230.2	10.4
50°-60°	136.4	6.2
60°-70°	90.7	4.1
70°-80°	48.6	2.2
80°-90°	13.4	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1209.6	54.8
0°-40°	1690.0	76.5
0°-60°	2056.6	93.1
0°-90°	2209.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2209.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1812	
5°	1791	168
15°	1587	446
25°	1303	595
35°	769	480
45°	284	230
55°	151	136
65°	91	91
75°	46	49
85°	10	13
90°	0	



TEST NUMBER: P204075

CATALOG NUMBER: LSR6B30D010BZ EC6B30508040 6LBNMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1811.9
2.5°	1811.9
5°	1790.8
7.5°	1755.7
10°	1706.6
12.5°	1653.9
15°	1587.2
17.5°	1524.0
20°	1453.7
22.5°	1380.0
25°	1302.7
27.5°	1222.0
30°	1106.1
32.5°	944.6
35°	769.0
37.5°	607.5
40°	470.5
42.5°	365.2
45°	284.4
47.5°	224.7
50°	189.6
52.5°	168.5
55°	151.0
57.5°	136.9
60°	119.4
62.5°	105.3
65°	91.3
67.5°	77.3
70°	66.7
72.5°	56.2
75°	45.6
77.5°	35.1
80°	28.1
82.5°	21.1
85°	10.5
87.5°	3.5
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)