

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P204972

Luminaire Tested: **LE_6B10D010 EC6B10209040 6LBCS1MMS**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204972
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B10D010 EC6B10209040 6LBCS1MMS
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH CAST MATTE METALLIC SILVER TRIM
WATTAGE D010TR-10.05 W DE010-10.58 W D5LT-10.2 W DMX-10.6 W DL2-11.8 W
DL3-11.1 W DLE-11.39 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1185.4 lumens
Efficiency: N/A
Efficacy: 119.7 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.27
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204972

CATALOG NUMBER: LE_6B10D010 EC6B10209040 6LBCS1MMS

Luminous Intensity Polar Plot





TEST NUMBER: P204972

CATALOG NUMBER: LE_6B10D010 EC6B10209040 6LBCS1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	111	107	103	100	108	105	101	98	100	98	95	97	94	92	93	91	90	88			88																
2	102	95	89	84	100	93	88	83	90	85	81	86	83	79	84	80	78	76			76																
3	94	85	77	72	92	83	76	71	80	74	70	77	73	69	75	71	67	65			65																
4	87	76	68	62	84	74	67	61	72	66	61	70	64	60	68	63	59	57			57																
5	80	68	60	54	78	67	59	54	65	58	53	63	57	53	61	56	52	50			50																
6	74	62	54	48	72	61	53	47	59	52	47	58	51	47	56	51	46	44			44																
7	69	56	48	42	67	56	48	42	54	47	42	53	46	42	51	46	41	40			40																
8	64	52	44	38	63	51	43	38	50	43	38	48	42	38	47	42	37	36			36																
9	60	48	40	35	59	47	40	34	46	39	34	45	39	34	44	38	34	32			32																
10	57	44	36	31	55	43	36	31	43	36	31	42	35	31	41	35	31	29			29																

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204972

CATALOG NUMBER: LE_6B10D010 EC6B10209040 6LBCS1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	51.3	4.3
10°-20°	144.0	12.1
20°-30°	210.3	17.7
30°-40°	240.5	20.3
40°-50°	231.1	19.5
50°-60°	178.4	15.1
60°-70°	99.6	8.4
70°-80°	28.9	2.4
80°-90°	1.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	405.6	34.2
0°-40°	646.1	54.5
0°-60°	1055.7	89.1
0°-90°	1185.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1185.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	544	
5°	540	51
15°	511	144
25°	457	210
35°	385	241
45°	301	231
55°	200	178
65°	100	100
75°	25	29
85°	1	1
90°	0	



TEST NUMBER: P204972

CATALOG NUMBER: LE_6B10D010 EC6B10209040 6LBCS1MMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	544.4
2.5°	544.4
5°	539.9
7.5°	537.5
10°	529.9
12.5°	520.6
15°	510.8
17.5°	500.8
20°	486.1
22.5°	474.6
25°	457.0
27.5°	439.4
30°	421.8
32.5°	404.1
35°	385.0
37.5°	365.8
40°	343.5
42.5°	323.6
45°	301.4
47.5°	276.0
50°	252.2
52.5°	226.2
55°	200.1
57.5°	173.2
60°	148.0
62.5°	122.8
65°	99.6
67.5°	78.2
70°	58.2
72.5°	40.6
75°	25.2
77.5°	13.0
80°	4.6
82.5°	1.5
85°	0.8
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)