

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P202839

Luminaire Tested: **LSR6B30D010BZ EC6B30508040 6LBWWH1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P202839  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LSR6B30D010BZ EC6B30508040 6LBWWH1  
Description: PORTFOLIO 6IN CYLINDER  
WIDE DISTRIBUTION WITH WHEAT TRIM  
WATTAGE D010TR-27.4 W DE010-27.95 W D5LT-27.65 W DMX-27.73 W DL2-29.56 W  
DL3-29.67 W DLE-29.73 W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2798.5 lumens  
Efficiency: N/A  
Efficacy: 99.9 lumens/watt  
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.18  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 28  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P202839

CATALOG NUMBER: LSR6B30D010BZ EC6B30508040 6LBWWH1

### Luminous Intensity Polar Plot





TEST NUMBER: P202839

CATALOG NUMBER: LSR6B30D010BZ EC6B30508040 6LBWWH1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	109	107	104	110	107	105	102	103	101	99	99	98	96	96	95	93	92																			
2	106	100	96	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83																			
3	99	92	86	81	97	90	85	81	88	83	79	85	81	78	83	80	77	75																			
4	93	84	78	73	91	83	77	72	81	76	71	79	74	71	77	73	70	68																			
5	87	77	71	66	85	76	70	65	75	69	65	73	68	64	71	67	63	62																			
6	82	71	64	59	80	71	64	59	69	63	59	67	62	58	66	61	58	56																			
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51																			
8	72	61	54	49	71	61	54	49	59	53	49	58	53	49	57	52	49	47																			
9	68	57	50	45	67	56	50	45	55	49	45	54	49	45	53	48	45	43																			
10	64	53	46	42	63	53	46	42	52	46	42	51	45	42	50	45	41	40																			

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P202839

CATALOG NUMBER: LSR6B30D010BZ EC6B30508040 6LBWWH1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	167.1	6.0
10°-20°	496.8	17.8
20°-30°	747.9	26.7
30°-40°	764.7	27.3
40°-50°	464.4	16.6
50°-60°	130.8	4.7
60°-70°	19.9	0.7
70°-80°	6.5	0.2
80°-90°	0.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1411.8	50.4
0°-40°	2176.5	77.8
0°-60°	2771.7	99.0
0°-90°	2798.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2798.5	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1738	
5°	1745	167
15°	1759	497
25°	1633	748
35°	1240	765
45°	597	464
55°	130	131
65°	18	20
75°	7	6
85°	0	0
90°	0	



TEST NUMBER: P202839

CATALOG NUMBER: LSR6B30D010BZ EC6B30508040 6LBWWH1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1738.2
2.5°	1738.2
5°	1745.2
7.5°	1755.7
10°	1755.7
12.5°	1762.8
15°	1759.3
17.5°	1752.2
20°	1727.7
22.5°	1692.5
25°	1632.8
27.5°	1566.1
30°	1474.8
32.5°	1366.0
35°	1239.6
37.5°	1099.1
40°	937.6
42.5°	769.0
45°	597.0
47.5°	442.4
50°	312.5
52.5°	210.7
55°	129.9
57.5°	77.3
60°	38.6
62.5°	24.6
65°	17.6
67.5°	14.0
70°	10.5
72.5°	7.0
75°	7.0
77.5°	3.5
80°	3.5
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)