

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P204351

Luminaire Tested: **LE_6B10D010 EC6B10209040 6LBSGPH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204351
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B10D010 EC6B10209040 6LBSGPH1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH GRAPHITE HAZE TRIM
WATTAGE D010TR-10.05 W DE010-10.58 W D5LT-10.2 W DMX-10.6 W DL2-11.8 W
DL3-11.1 W DLE-11.39 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1101.4 lumens
Efficiency: N/A
Efficacy: 111.2 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.26
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204351

CATALOG NUMBER: LE_6B10D010 EC6B10209040 6LBSGPH1

Luminous Intensity Polar Plot





TEST NUMBER: P204351

CATALOG NUMBER: LE_6B10D010 EC6B10209040 6LBSGPH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	103	100	108	105	102	99	101	98	96	97	95	93	93	92	90	88			
2	102	95	89	84	100	93	88	83	90	85	82	87	83	80	84	81	78	76			
3	94	85	78	72	92	83	77	71	80	75	70	78	73	69	75	71	68	66			
4	87	76	68	62	85	75	67	62	72	66	61	70	65	60	68	63	59	57			
5	80	68	60	54	78	67	60	54	65	59	53	63	58	53	62	56	52	50			
6	74	62	54	48	73	61	53	48	59	52	47	58	52	47	56	51	47	45			
7	69	57	48	43	68	56	48	43	54	47	42	53	47	42	52	46	42	40			
8	65	52	44	38	63	51	44	38	50	43	38	49	42	38	48	42	38	36			
9	60	48	40	35	59	47	40	35	46	39	35	45	39	34	44	38	34	32			
10	57	44	37	32	56	44	36	32	43	36	32	42	36	31	41	35	31	30			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204351

CATALOG NUMBER: LE_6B10D010 EC6B10209040 6LBSGPH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	48.2	4.4
10°-20°	135.2	12.3
20°-30°	197.2	17.9
30°-40°	224.8	20.4
40°-50°	215.7	19.6
50°-60°	165.2	15.0
60°-70°	90.6	8.2
70°-80°	24.1	2.2
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	380.6	34.6
0°-40°	605.4	55.0
0°-60°	986.3	89.6
0°-90°	1101.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1101.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	512	
5°	508	48
15°	480	135
25°	428	197
35°	360	225
45°	280	216
55°	185	165
65°	91	91
75°	21	24
85°	0	0
90°	0	



TEST NUMBER: P204351

CATALOG NUMBER: LE_6B10D010 EC6B10209040 6LBSGPH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	511.5
2.5°	510.2
5°	507.6
7.5°	503.6
10°	498.4
12.5°	489.1
15°	479.9
17.5°	469.2
20°	457.4
22.5°	442.9
25°	428.2
27.5°	413.8
30°	395.2
32.5°	378.0
35°	359.5
37.5°	341.0
40°	322.5
42.5°	302.8
45°	280.2
47.5°	257.8
50°	234.0
52.5°	208.9
55°	185.0
57.5°	161.2
60°	136.1
62.5°	112.4
65°	91.2
67.5°	70.0
70°	51.5
72.5°	34.4
75°	21.1
77.5°	9.2
80°	2.6
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)