

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P203051

Luminaire Tested: **LSR6B30D010BZ EC6B30509040 6LBWB1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P203051  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LSR6B30D010BZ EC6B30509040 6LBWB1  
Description: PORTFOLIO 6IN CYLINDER  
WIDE DISTRIBUTION WITH SPECULAR BLACK TRIM  
WATTAGE D010TR-27.4 W DE010-27.95 W D5LT-27.65 W DMX-27.73 W DL2-29.56 W  
DL3-29.67 W DLE-29.73 W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1442.5 lumens  
Efficiency: N/A  
Efficacy: 51.5 lumens/watt  
Spacing Criteria (0/90/45): 1.08 / 1.08 / 1.08  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 28  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P203051

CATALOG NUMBER: LSR6B30D010BZ EC6B30509040 6LBWB1

### Luminous Intensity Polar Plot





TEST NUMBER: P203051

CATALOG NUMBER: LSR6B30D010BZ EC6B30509040 6LBWB1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20																		
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR	0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	98	97	96	95	94	92	92	92	84																	
	1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92	92	92	90	88	86	84	81	78	77	77																	
	2	106	101	97	93	104	99	95	92	96	93	90	93	90	88	90	88	86	84	84	81	78	77	77	77	77	77	77	77																	
	3	100	93	87	83	98	92	86	82	89	85	81	86	83	80	84	81	78	77	77	77	77	77	77	77	77	77	77	77																	
	4	94	86	79	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70	70	70	70	70	70	70	70	70	70	70																	
	5	89	79	73	68	87	78	72	67	76	71	67	75	70	66	73	69	66	64	64	64	64	64	64	64	64	64	64	64																	
	6	83	73	67	62	82	72	66	61	71	65	61	69	64	61	68	64	60	59	59	59	59	59	59	59	59	59	59	59																	
	7	78	68	61	56	77	67	61	56	66	60	56	65	60	56	63	59	55	54	54	54	54	54	54	54	54	54	54	54																	
	8	74	63	57	52	73	63	56	52	61	56	52	60	55	51	59	55	51	50	50	50	50	50	50	50	50	50	50	50																	
	9	70	59	52	48	69	58	52	48	57	52	48	57	51	47	56	51	47	46	46	46	46	46	46	46	46	46	46	46																	
	10	66	55	49	44	65	55	49	44	54	48	44	53	48	44	52	47	44	42	42	42	42	42	42	42	42	42	42	42																	

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P203051

CATALOG NUMBER: LSR6B30D010BZ EC6B30509040 6LBWB1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	102.2	7.1
10°-20°	285.8	19.8
20°-30°	400.4	27.8
30°-40°	382.4	26.5
40°-50°	217.8	15.1
50°-60°	53.2	3.7
60°-70°	0.7	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	788.4	54.7
0°-40°	1170.8	81.2
0°-60°	1441.8	100.0
0°-90°	1442.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1442.5	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1087	
5°	1078	102
15°	1014	286
25°	876	400
35°	623	382
45°	279	218
55°	53	53
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P203051

CATALOG NUMBER: LSR6B30D010BZ EC6B30509040 6LBWB1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1087.1
2.5°	1087.1
5°	1078.3
7.5°	1066.5
10°	1057.7
12.5°	1040.1
15°	1013.6
17.5°	990.1
20°	960.8
22.5°	922.6
25°	875.6
27.5°	822.7
30°	763.9
32.5°	693.4
35°	622.9
37.5°	537.7
40°	446.6
42.5°	361.4
45°	279.1
47.5°	205.7
50°	144.0
52.5°	91.1
55°	52.9
57.5°	23.5
60°	5.9
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)