

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P203252

Luminaire Tested: **LSR6B30D010BZ EC6B30508050 6LBMH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203252
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR6B30D010BZ EC6B30508050 6LBMH1
Description: PORTFOLIO 6IN CYLINDER
MEDIUM DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM
WATTAGE D010TR-27.4 W DE010-27.95 W D5LT-27.65 W DMX-27.73 W DL2-29.56 W
DL3-29.67 W DLE-29.73 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2236.2 lumens
Efficiency: N/A
Efficacy: 79.9 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.93
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203252

CATALOG NUMBER: LSR6B30D010BZ EC6B30508050 6LBMH1

Luminous Intensity Polar Plot





TEST NUMBER: P203252

CATALOG NUMBER: LSR6B30D010BZ EC6B30508050 6LBMH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20																	
RC	80									70									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																								
RCR																																																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																																				
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	92																																				
2	107	102	97	93	105	100	96	92	97	93	90	94	91	88	91	89	87	85																																				
3	101	94	88	84	99	92	87	84	90	86	82	87	84	81	85	82	80	78																																				
4	95	87	81	76	93	86	80	76	84	79	75	82	78	74	80	76	73	72																																				
5	90	81	75	70	88	80	74	70	78	73	69	76	72	68	75	71	68	66																																				
6	85	75	69	64	83	75	69	64	73	68	64	72	67	63	70	66	63	61																																				
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																																				
8	76	66	60	55	75	65	59	55	64	59	55	63	58	55	62	58	54	53																																				
9	72	62	56	51	71	61	55	51	60	55	51	60	55	51	59	54	51	49																																				
10	69	58	52	48	68	58	52	48	57	52	48	56	51	48	55	51	48	46																																				

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203252

CATALOG NUMBER: LSR6B30D010BZ EC6B30508050 6LBMH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	202.3	9.0
10°-20°	523.4	23.4
20°-30°	678.2	30.3
30°-40°	503.5	22.5
40°-50°	212.6	9.5
50°-60°	75.5	3.4
60°-70°	29.1	1.3
70°-80°	10.1	0.5
80°-90°	1.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1404.0	62.8
0°-40°	1907.6	85.3
0°-60°	2195.6	98.2
0°-90°	2236.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2236.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2213	
5°	2165	202
15°	1868	523
25°	1504	678
35°	798	504
45°	262	213
55°	80	75
65°	29	29
75°	10	10
85°	0	1
90°	0	



TEST NUMBER: P203252

CATALOG NUMBER: LSR6B30D010BZ EC6B30508050 6LBMH1

CANDELA DISTRIBUTION (FULL):

0°	
0°	2212.9
2.5°	2206.6
5°	2165.0
7.5°	2104.4
10°	2030.9
12.5°	1951.1
15°	1868.1
17.5°	1775.5
20°	1692.4
22.5°	1606.2
25°	1504.0
27.5°	1363.5
30°	1197.5
32.5°	1002.7
35°	798.3
37.5°	625.9
40°	475.8
42.5°	354.5
45°	261.8
47.5°	191.6
50°	140.5
52.5°	105.4
55°	79.8
57.5°	60.7
60°	47.9
62.5°	35.1
65°	28.7
67.5°	22.4
70°	16.0
72.5°	12.8
75°	9.6
77.5°	6.4
80°	3.2
82.5°	3.2
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)