

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P205385

Luminaire Tested: **LE_6B15D010 EC6B10209024 6LBSLI1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P205385
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B15D010 EC6B10209024 6LBSLI1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH SPECULAR CLEAR TRIM
WATTAGE D010TR-14.39 W DE010-14.29 W D5LT-14.34 W DMX-14.46 W DL2-15.8 W
DL3-15.28 W DLE-15.432 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1428.1 lumens
Efficiency: N/A
Efficacy: 99.9 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 1.04
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P205385

CATALOG NUMBER: LE_6B15D010 EC6B10209024 6LBSLI1

Luminous Intensity Polar Plot





TEST NUMBER: P205385

CATALOG NUMBER: LE_6B15D010 EC6B10209024 6LBSLI1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	111	107	104	101	109	105	102	99	101	99	96	97	95	93	94	92	91	89				89
2	103	96	91	86	100	94	89	85	91	87	83	88	84	81	85	82	79	77				77
3	95	86	79	74	93	85	78	73	82	76	72	79	75	71	77	73	70	68				68
4	88	78	70	64	86	77	69	64	74	68	63	72	67	62	70	65	62	60				60
5	82	71	63	57	80	70	62	57	67	61	56	66	60	55	64	59	55	53				53
6	76	64	56	51	74	63	56	51	62	55	50	60	54	50	59	53	49	47				47
7	71	59	51	46	70	58	51	45	57	50	45	55	49	45	54	49	45	43				43
8	67	54	47	41	65	54	46	41	52	46	41	51	45	41	50	45	41	39				39
9	63	50	43	38	61	50	43	38	49	42	38	48	42	37	47	41	37	36				36
10	59	47	40	35	58	46	39	35	45	39	35	45	39	34	44	38	34	33				33

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P205385

CATALOG NUMBER: LE_6B15D010 EC6B10209024 6LBSLI1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	83.1	5.8
10°-20°	211.4	14.8
20°-30°	269.6	18.9
30°-40°	279.6	19.6
40°-50°	257.6	18.0
50°-60°	193.8	13.6
60°-70°	104.6	7.3
70°-80°	28.0	2.0
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	564.1	39.5
0°-40°	843.6	59.1
0°-60°	1295.0	90.7
0°-90°	1428.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1428.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	901	
5°	888	83
15°	754	211
25°	586	270
35°	446	280
45°	335	258
55°	217	194
65°	105	105
75°	24	28
85°	0	0
90°	0	



TEST NUMBER: P205385

CATALOG NUMBER: LE_6B15D010 EC6B10209024 6LBSLI1

CANDELA DISTRIBUTION (FULL):

	0°
0°	901.2
2.5°	898.2
5°	887.6
7.5°	867.9
10°	833.0
12.5°	798.0
15°	754.0
17.5°	713.1
20°	670.6
22.5°	626.6
25°	585.6
27.5°	546.2
30°	509.8
32.5°	476.4
35°	446.0
37.5°	417.2
40°	389.9
42.5°	361.1
45°	335.2
47.5°	306.5
50°	277.6
52.5°	247.2
55°	217.0
57.5°	186.6
60°	157.8
62.5°	130.5
65°	104.8
67.5°	80.4
70°	59.1
72.5°	41.0
75°	24.2
77.5°	10.6
80°	3.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)