

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P203532

Luminaire Tested: **LE_6B15D010 EC6B10208030 6LBMMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203532
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B15D010 EC6B10208030 6LBMMW1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
MEDIUM DISTRIBUTION WITH MATTE WHITE TRIM
WATTAGE D010TR-14.39 W DE010-14.29 W D5LT-14.34 W DMX-14.46 W DL2-15.8 W
DL3-15.28 W DLE-15.432 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1469.7 lumens
Efficiency: N/A
Efficacy: 102.8 lumens/watt
Spacing Criteria (0/90/45): 1 / 1 / 0.97
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203532

CATALOG NUMBER: LE_6B15D010 EC6B10208030 6LBMMW1

Luminous Intensity Polar Plot





TEST NUMBER: P203532

CATALOG NUMBER: LE_6B15D010 EC6B10208030 6LBMMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	108	104	101	109	105	103	100	101	99	97	98	96	94	94	92	91	89			
2	104	97	92	88	101	96	91	87	92	88	85	89	86	83	86	83	81	79			
3	97	88	82	77	95	87	81	76	84	79	75	82	77	74	79	76	73	71			
4	90	81	74	68	88	80	73	68	77	72	67	75	70	66	73	69	65	64			
5	85	74	67	61	83	73	66	61	71	65	61	69	64	60	68	63	59	58			
6	79	68	61	56	78	68	61	56	66	60	55	64	59	55	63	58	54	53			
7	75	63	56	51	73	63	56	51	61	55	50	60	54	50	59	54	50	48			
8	70	59	52	47	69	58	51	47	57	51	46	56	50	46	55	50	46	44			
9	66	55	48	43	65	54	48	43	53	47	43	52	47	43	51	46	43	41			
10	63	51	45	40	62	51	44	40	50	44	40	49	44	40	48	43	40	38			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203532

CATALOG NUMBER: LE_6B15D010 EC6B10208030 6LBMMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	101.3	6.9
10°-20°	271.3	18.5
20°-30°	364.4	24.8
30°-40°	298.9	20.3
40°-50°	179.5	12.2
50°-60°	119.3	8.1
60°-70°	79.9	5.4
70°-80°	43.0	2.9
80°-90°	12.1	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	737.0	50.1
0°-40°	1035.9	70.5
0°-60°	1334.6	90.8
0°-90°	1469.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1469.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1097	
5°	1078	101
15°	967	271
25°	803	364
35°	474	299
45°	227	179
55°	132	119
65°	81	80
75°	40	43
85°	10	12
90°	0	



TEST NUMBER: P203532

CATALOG NUMBER: LE_6B15D010 EC6B10208030 6LBMMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1096.6
2.5°	1088.5
5°	1078.4
7.5°	1056.1
10°	1029.8
12.5°	997.2
15°	966.9
17.5°	930.4
20°	893.9
22.5°	853.4
25°	802.8
27.5°	741.9
30°	660.8
32.5°	569.6
35°	474.4
37.5°	393.2
40°	324.4
42.5°	269.6
45°	227.0
47.5°	192.6
50°	168.2
52.5°	148.0
55°	131.8
57.5°	117.6
60°	105.4
62.5°	91.2
65°	81.1
67.5°	68.9
70°	58.8
72.5°	48.6
75°	40.5
77.5°	32.4
80°	24.4
82.5°	18.2
85°	10.1
87.5°	4.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)