

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P203120

Luminaire Tested: **LE_6B15D010 EC6B10208030 6LBWMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203120
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B15D010 EC6B10208030 6LBWMW1
Description: PORTFOLIO 6 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT
WIDE DISTRIBUTION WITH MATTE WHITE TRIM
WATTAGE D010TR-14.39 W DE010-14.29 W D5LT-14.34 W DMX-14.46 W DL2-15.8 W
DL3-15.28 W DLE-15.432 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1732.2 lumens
Efficiency: N/A
Efficacy: 121.1 lumens/watt
Spacing Criteria (0/90/45): 1.13 / 1.13 / 1.15
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203120

CATALOG NUMBER: LE_6B15D010 EC6B10208030 6LBWMW1

Luminous Intensity Polar Plot





TEST NUMBER: P203120

CATALOG NUMBER: LE_6B15D010 EC6B10208030 6LBWMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	100	108	105	102	99	101	98	96	97	95	93	93	92	90	88			
2	103	96	90	86	100	94	89	85	91	86	83	88	84	81	85	82	79	77			
3	95	86	80	74	93	85	79	74	82	77	72	80	75	71	77	73	70	68			
4	89	78	71	65	86	77	70	65	75	69	64	72	67	63	70	66	62	60			
5	82	71	64	58	80	70	63	58	68	62	57	66	61	56	65	60	56	54			
6	77	65	57	52	75	64	57	52	63	56	51	61	55	51	60	54	50	49			
7	72	60	52	47	70	59	52	47	58	51	46	56	50	46	55	50	46	44			
8	67	55	48	42	66	55	47	42	53	47	42	52	46	42	51	46	42	40			
9	63	51	44	39	62	51	44	39	50	43	39	49	43	38	48	42	38	37			
10	60	48	40	36	58	47	40	36	46	40	36	45	40	35	45	39	35	34			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203120

CATALOG NUMBER: LE_6B15D010 EC6B10208030 6LBWMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	91.6	5.3
10°-20°	256.9	14.8
20°-30°	370.2	21.4
30°-40°	384.3	22.2
40°-50°	284.1	16.4
50°-60°	169.7	9.8
60°-70°	103.2	6.0
70°-80°	56.5	3.3
80°-90°	15.7	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	718.7	41.5
0°-40°	1103.0	63.7
0°-60°	1556.8	89.9
0°-90°	1732.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1732.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	973	
5°	966	92
15°	912	257
25°	807	370
35°	620	384
45°	366	284
55°	185	170
65°	103	103
75°	52	56
85°	13	16
90°	0	



TEST NUMBER: P203120

CATALOG NUMBER: LE_6B15D010 EC6B10208030 6LBWMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	972.8
2.5°	972.8
5°	966.4
7.5°	958.0
10°	945.4
12.5°	930.6
15°	911.8
17.5°	890.8
20°	869.8
22.5°	840.4
25°	806.8
27.5°	771.0
30°	724.8
32.5°	678.6
35°	619.8
37.5°	558.9
40°	491.6
42.5°	426.5
45°	365.5
47.5°	310.9
50°	262.6
52.5°	220.6
55°	184.9
57.5°	157.6
60°	134.5
62.5°	117.6
65°	103.0
67.5°	90.4
70°	77.8
72.5°	65.1
75°	52.5
77.5°	42.0
80°	31.5
82.5°	23.1
85°	12.6
87.5°	6.2
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)