

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P205083

Luminaire Tested: **LE_6B15D010 EC6B10209030 6LBMLI1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P205083
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B15D010 EC6B10209030 6LBML1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
MEDIUM DISTRIBUTION WITH SPECULAR CLEAR TRIM
WATTAGE D010TR-14.39 W DE010-14.29 W D5LT-14.34 W DMX-14.46 W DL2-15.8 W
DL3-15.28 W DLE-15.432 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1400.9 lumens
Efficiency: N/A
Efficacy: 98.0 lumens/watt
Spacing Criteria (0/90/45): 0.85 / 0.85 / 0.85
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P205083

CATALOG NUMBER: LE_6B15D010 EC6B10209030 6LBMLI1

Luminous Intensity Polar Plot





TEST NUMBER: P205083

CATALOG NUMBER: LE_6B15D010 EC6B10209030 6LBMLI1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20																	
RC	80									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0															
RCR																																													
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																											
1	114	111	109	106	111	109	107	105	105	103	101	101	100	98	98	97	96	94																											
2	108	103	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88																											
3	103	97	92	88	101	95	91	87	93	89	86	90	87	85	88	85	83	82																											
4	98	91	85	81	96	89	84	81	87	83	80	85	82	79	83	80	78	76																											
5	93	85	79	75	91	84	79	75	82	78	74	81	77	73	79	76	73	71																											
6	89	80	74	70	87	79	74	70	78	73	69	76	72	69	75	71	68	67																											
7	84	75	69	65	83	75	69	65	73	68	65	72	68	64	71	67	64	63																											
8	80	71	65	61	79	70	65	61	69	64	61	68	64	60	67	63	60	59																											
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55																											
10	73	64	58	54	72	63	58	54	62	57	54	62	57	54	61	57	54	52																											

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P205083

CATALOG NUMBER: LE_6B15D010 EC6B10209030 6LBMLI1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	161.5	11.5
10°-20°	402.1	28.7
20°-30°	467.4	33.4
30°-40°	286.2	20.4
40°-50°	71.1	5.1
50°-60°	8.3	0.6
60°-70°	3.1	0.2
70°-80°	1.2	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1031.0	73.6
0°-40°	1317.2	94.0
0°-60°	1396.6	99.7
0°-90°	1400.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1400.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1753	
5°	1730	162
15°	1443	402
25°	1034	467
35°	448	286
45°	79	71
55°	7	8
65°	4	3
75°	2	1
85°	0	0
90°	0	



TEST NUMBER: P205083

CATALOG NUMBER: LE_6B15D010 EC6B10209030 6LBMLI1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1753.1
2.5°	1751.4
5°	1729.9
7.5°	1683.2
10°	1620.5
12.5°	1538.0
15°	1443.0
17.5°	1340.9
20°	1240.5
22.5°	1140.1
25°	1034.4
27.5°	912.5
30°	772.6
32.5°	609.5
35°	448.1
37.5°	315.5
40°	215.1
42.5°	134.5
45°	78.9
47.5°	44.9
50°	23.2
52.5°	10.8
55°	7.1
57.5°	5.4
60°	5.4
62.5°	3.6
65°	3.6
67.5°	1.8
70°	1.8
72.5°	1.8
75°	1.8
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)