

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P202943

Luminaire Tested: **LSR6B30D010BZ EC6B30508050 6LBWGPH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P202943
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR6B30D010BZ EC6B30508050 6LBWGPH1
Description: PORTFOLIO 6IN CYLINDER
WIDE DISTRIBUTIONWITH GRAPHITE HAZE TRIM
WATTAGE D010TR-27.4 W DE010-27.95 W D5LT-27.65 W DMX-27.73 W DL2-29.56 W
DL3-29.67 W DLE-29.73 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2036.3 lumens
Efficiency: N/A
Efficacy: 72.7 lumens/watt
Spacing Criteria (0/90/45): 1.11 / 1.11 / 1.11
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P202943

CATALOG NUMBER: LSR6B30D010BZ EC6B30508050 6LBWGPH1

Luminous Intensity Polar Plot





TEST NUMBER: P202943

CATALOG NUMBER: LSR6B30D010BZ EC6B30508050 6LBWGPH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	109	106	104	110	107	104	102	103	101	99	99	98	96	96	94	93	91			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	86	84	82			
3	99	91	85	81	97	90	84	80	87	82	79	85	81	77	82	79	76	74			
4	93	84	77	72	91	82	76	72	80	75	71	78	74	70	76	72	69	67			
5	87	77	70	65	85	76	69	65	74	68	64	72	67	63	71	66	63	61			
6	81	71	64	59	80	70	63	59	68	62	58	67	62	58	65	61	57	56			
7	76	65	58	53	75	65	58	53	63	57	53	62	57	53	61	56	52	51			
8	72	61	54	49	70	60	53	49	59	53	49	58	52	48	57	52	48	47			
9	68	57	50	45	66	56	49	45	55	49	45	54	48	45	53	48	44	43			
10	64	53	46	42	63	52	46	42	51	45	41	51	45	41	50	45	41	40			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P202943

CATALOG NUMBER: LSR6B30D010BZ EC6B30508050 6LBWGPH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	130.4	6.4
10°-20°	365.6	18.0
20°-30°	523.1	25.7
30°-40°	521.4	25.6
40°-50°	332.1	16.3
50°-60°	122.5	6.0
60°-70°	30.6	1.5
70°-80°	9.2	0.5
80°-90°	1.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1019.1	50.0
0°-40°	1540.5	75.7
0°-60°	1995.1	98.0
0°-90°	2036.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2036.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1384	
5°	1377	130
15°	1300	366
25°	1142	523
35°	848	521
45°	428	332
55°	130	122
65°	28	31
75°	7	9
85°	0	1
90°	0	



TEST NUMBER: P202943

CATALOG NUMBER: LSR6B30D010BZ EC6B30508050 6LBWGPH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1384.0
2.5°	1384.0
5°	1377.0
7.5°	1363.0
10°	1345.5
12.5°	1324.5
15°	1299.9
17.5°	1268.4
20°	1233.4
22.5°	1194.8
25°	1142.3
27.5°	1086.2
30°	1012.6
32.5°	935.5
35°	847.9
37.5°	742.8
40°	634.2
42.5°	529.1
45°	427.5
47.5°	336.4
50°	252.3
52.5°	185.7
55°	129.6
57.5°	84.1
60°	56.1
62.5°	38.5
65°	28.0
67.5°	21.0
70°	17.5
72.5°	10.5
75°	7.0
77.5°	7.0
80°	3.5
82.5°	3.5
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)