

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P204362

Luminaire Tested: **LE_6B15D010 EC6B10209030 6LBSGPH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204362
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B15D010 EC6B10209030 6LBSGPH1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH GRAPHITE HAZE TRIM
WATTAGE D010TR-14.39 W DE010-14.29 W D5LT-14.34 W DMX-14.46 W DL2-15.8 W
DL3-15.28 W DLE-15.432 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1496.0 lumens
Efficiency: N/A
Efficacy: 104.6 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.26
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204362

CATALOG NUMBER: LE_6B15D010 EC6B10209030 6LBSGPH1

Luminous Intensity Polar Plot





TEST NUMBER: P204362

CATALOG NUMBER: LE_6B15D010 EC6B10209030 6LBSGPH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	103	100	108	105	102	99	101	98	96	97	95	93	93	91	90	88			
2	102	95	89	84	100	93	88	83	90	85	82	87	83	80	84	81	78	76			
3	94	85	78	72	92	83	77	71	80	75	70	78	73	69	75	71	68	66			
4	87	76	68	62	85	75	67	62	72	66	61	70	65	60	68	63	59	57			
5	80	68	60	54	78	67	60	54	65	59	53	63	58	53	62	56	52	50			
6	74	62	54	48	73	61	53	48	59	52	47	58	52	47	56	51	47	45			
7	69	57	48	43	68	56	48	43	54	47	42	53	47	42	52	46	42	40			
8	65	52	44	38	63	51	44	38	50	43	38	49	42	38	48	42	38	36			
9	60	48	40	35	59	47	40	35	46	39	35	45	39	34	44	38	34	32			
10	57	44	37	32	56	44	36	32	43	36	32	42	36	31	41	35	31	30			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204362

CATALOG NUMBER: LE_6B15D010 EC6B10209030 6LBSGPH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	65.4	4.4
10°-20°	183.6	12.3
20°-30°	267.8	17.9
30°-40°	305.4	20.4
40°-50°	293.0	19.6
50°-60°	224.4	15.0
60°-70°	123.1	8.2
70°-80°	32.7	2.2
80°-90°	0.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	516.9	34.6
0°-40°	822.3	55.0
0°-60°	1339.7	89.5
0°-90°	1496.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1496.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	695	
5°	689	65
15°	652	184
25°	582	268
35°	488	305
45°	381	293
55°	251	224
65°	124	123
75°	29	33
85°	0	0
90°	0	



TEST NUMBER: P204362

CATALOG NUMBER: LE_6B15D010 EC6B10209030 6LBSGPH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	694.8
2.5°	693.0
5°	689.4
7.5°	684.0
10°	676.9
12.5°	664.2
15°	651.8
17.5°	637.4
20°	621.2
22.5°	601.5
25°	581.8
27.5°	562.0
30°	536.8
32.5°	513.5
35°	488.4
37.5°	463.2
40°	438.1
42.5°	411.1
45°	380.6
47.5°	350.1
50°	317.8
52.5°	283.6
55°	251.4
57.5°	219.0
60°	184.9
62.5°	152.6
65°	123.9
67.5°	95.1
70°	70.0
72.5°	46.6
75°	28.8
77.5°	12.6
80°	3.6
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)