

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P205011

Luminaire Tested: **LSR6B30D010BZ EC6B30509050 6LBSCMMS1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P205011  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LSR6B30D010BZ EC6B30509050 6LBCSMMS1  
Description: PORTFOLIO 6IN CYLINDER  
SHALLOW DISTRIBUTION WITH CAST MATTE METALLIC SILVER TRIM  
WATTAGE D010TR-27.4 W DE010-27.95 W D5LT-27.65 W DMX-27.73 W DL2-29.56 W  
DL3-29.67 W DLE-29.73 W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2648.7 lumens  
Efficiency: N/A  
Efficacy: 94.6 lumens/watt  
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.27  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 28  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P205011

CATALOG NUMBER: LSR6B30D010BZ EC6B30509050 6LBCSMMS1

### Luminous Intensity Polar Plot





TEST NUMBER: P205011

CATALOG NUMBER: LSR6B30D010BZ EC6B30509050 6LBCSMMS1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	111	107	103	100	108	105	101	98	100	98	95	97	94	92	93	91	90	88	88	88	88
2	102	95	89	84	100	93	88	83	90	85	81	86	83	79	83	80	78	76	76	76	76
3	94	85	77	72	92	83	76	71	80	74	70	77	73	69	75	71	67	65	65	65	65
4	87	76	68	62	84	74	67	61	72	66	61	70	64	60	68	63	59	57	57	57	57
5	80	68	60	54	78	67	59	54	65	58	53	63	57	53	61	56	52	50	50	50	50
6	74	62	54	48	72	61	53	47	59	52	47	58	51	47	56	51	46	44	44	44	44
7	69	56	48	42	67	56	48	42	54	47	42	53	46	42	51	46	41	40	40	40	40
8	64	52	44	38	63	51	43	38	50	43	38	48	42	38	47	42	37	36	36	36	36
9	60	48	40	35	59	47	40	34	46	39	34	45	39	34	44	38	34	32	32	32	32
10	57	44	36	31	55	43	36	31	43	36	31	42	35	31	41	35	31	29	29	29	29

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P205011

CATALOG NUMBER: LSR6B30D010BZ EC6B30509050 6LBCSMMS1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	114.6	4.3
10°-20°	321.6	12.1
20°-30°	469.8	17.7
30°-40°	537.3	20.3
40°-50°	516.4	19.5
50°-60°	398.8	15.1
60°-70°	222.5	8.4
70°-80°	64.8	2.4
80°-90°	2.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	906.1	34.2
0°-40°	1443.4	54.5
0°-60°	2358.6	89.0
0°-90°	2648.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2648.7	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1216	
5°	1206	115
15°	1141	322
25°	1021	470
35°	860	537
45°	673	516
55°	447	399
65°	223	223
75°	56	65
85°	2	3
90°	0	



TEST NUMBER: P205011

CATALOG NUMBER: LSR6B30D010BZ EC6B30509050 6LBCSMMS1

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1216.4
2.5°	1216.4
5°	1206.1
7.5°	1200.9
10°	1183.8
12.5°	1163.2
15°	1141.0
17.5°	1118.7
20°	1086.2
22.5°	1060.5
25°	1021.1
27.5°	981.7
30°	942.2
32.5°	902.8
35°	860.0
37.5°	817.2
40°	767.5
42.5°	723.0
45°	673.3
47.5°	616.7
50°	563.6
52.5°	505.4
55°	447.1
57.5°	387.2
60°	330.6
62.5°	274.1
65°	222.7
67.5°	174.7
70°	130.2
72.5°	90.8
75°	56.5
77.5°	29.1
80°	10.3
82.5°	3.4
85°	1.7
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)