

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204494

Luminaire Tested: **LSR6B30D010BZ EC6B30509050 6LBSB1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P204494  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LSR6B30D010BZ EC6B30509050 6LBSB1  
Description: PORTFOLIO 6IN CYLINDER  
SHALLOW DISTRIBUTION WITH SPECULAR BLACK TRIM  
WATTAGE D010TR-27.4 W DE010-27.95 W D5LT-27.65 W DMX-27.73 W DL2-29.56 W  
DL3-29.67 W DLE-29.73 W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2357.4 lumens  
Efficiency: N/A  
Efficacy: 84.2 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.2 / 1.3  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 28  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P204494

CATALOG NUMBER: LSR6B30D010BZ EC6B30509050 6LBSB1

### Luminous Intensity Polar Plot





TEST NUMBER: P204494

CATALOG NUMBER: LSR6B30D010BZ EC6B30509050 6LBSB1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	103	100	108	105	101	98	100	98	95	97	94	93	93	91	90	88			
2	102	95	89	84	100	93	88	83	90	85	81	86	83	79	84	80	78	76			
3	94	84	77	72	91	83	76	71	80	74	70	77	73	68	75	71	67	65			
4	86	76	68	62	84	74	67	61	72	65	60	70	64	60	68	63	59	57			
5	80	68	60	54	78	67	59	53	65	58	53	63	57	52	61	56	52	50			
6	74	62	53	47	72	61	53	47	59	52	47	57	51	46	56	50	46	44			
7	69	56	48	42	67	55	48	42	54	47	42	52	46	41	51	45	41	39			
8	64	51	43	38	63	51	43	38	49	42	37	48	42	37	47	41	37	35			
9	60	47	39	34	59	47	39	34	46	39	34	45	38	34	44	38	34	32			
10	56	44	36	31	55	43	36	31	42	36	31	41	35	31	40	35	31	29			

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P204494

CATALOG NUMBER: LSR6B30D010BZ EC6B30509050 6LBSB1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	98.2	4.2
10°-20°	278.5	11.8
20°-30°	414.3	17.6
30°-40°	482.1	20.5
40°-50°	469.9	19.9
50°-60°	361.4	15.3
60°-70°	199.8	8.5
70°-80°	52.9	2.2
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	790.9	33.6
0°-40°	1273.0	54.0
0°-60°	2104.3	89.3
0°-90°	2357.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2357.4	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1040	
5°	1034	98
15°	986	278
25°	900	414
35°	774	482
45°	610	470
55°	403	361
65°	200	200
75°	45	53
85°	0	0
90°	0	



TEST NUMBER: P204494

CATALOG NUMBER: LSR6B30D010BZ EC6B30509050 6LBSB1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1040.0
2.5°	1040.0
5°	1034.0
7.5°	1025.0
10°	1019.0
12.5°	1001.1
15°	986.2
17.5°	971.2
20°	950.3
22.5°	929.4
25°	899.5
27.5°	869.6
30°	839.7
32.5°	806.9
35°	774.0
37.5°	732.2
40°	696.3
42.5°	657.4
45°	609.6
47.5°	564.8
50°	514.0
52.5°	460.2
55°	403.4
57.5°	349.6
60°	298.8
62.5°	248.0
65°	200.2
67.5°	155.4
70°	113.6
72.5°	77.7
75°	44.8
77.5°	20.9
80°	3.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)