

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204288

Luminaire Tested: **LSR6B30D010BZ EC6B30509050 6LBSWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204288
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR6B30D010BZ EC6B30509050 6LBSWH1
Description: PORTFOLIO 6IN CYLINDER
SHALLOW DISTRIBUTION WITH WHEAT TRIM
WATTAGE D010TR-27.4 W DE010-27.95 W D5LT-27.65 W DMX-27.73 W DL2-29.56 W
DL3-29.67 W DLE-29.73 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2696.8 lumens
Efficiency: N/A
Efficacy: 96.3 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1.08
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204288

CATALOG NUMBER: LSR6B30D010BZ EC6B30509050 6LBSWH1

Luminous Intensity Polar Plot





TEST NUMBER: P204288

CATALOG NUMBER: LSR6B30D010BZ EC6B30509050 6LBSWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	94	92	90	89																			
2	103	96	90	85	100	94	89	84	91	86	83	87	84	81	85	82	79	77																			
3	95	86	79	73	93	84	78	73	82	76	72	79	74	70	76	73	69	67																			
4	88	77	70	64	86	76	69	63	74	68	63	72	66	62	69	65	61	59																			
5	81	70	62	56	79	69	62	56	67	60	55	65	59	55	63	58	54	52																			
6	76	64	56	50	74	63	55	50	61	54	49	60	54	49	58	53	49	47																			
7	71	58	51	45	69	58	50	45	56	49	45	55	49	44	54	48	44	42																			
8	66	54	46	41	65	53	46	41	52	45	40	51	45	40	50	44	40	38																			
9	62	50	42	37	61	49	42	37	48	41	37	47	41	37	46	41	37	35																			
10	58	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32																			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204288

CATALOG NUMBER: LSR6B30D010BZ EC6B30509050 6LBSWH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	148.3	5.5
10°-20°	384.0	14.2
20°-30°	502.2	18.6
30°-40°	531.8	19.7
40°-50°	496.0	18.4
50°-60°	375.7	13.9
60°-70°	203.5	7.5
70°-80°	54.6	2.0
80°-90°	0.8	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1034.5	38.4
0°-40°	1566.3	58.1
0°-60°	2437.9	90.4
0°-90°	2696.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2696.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1608	
5°	1585	148
15°	1372	384
25°	1092	502
35°	850	532
45°	646	496
55°	422	376
65°	204	203
75°	47	55
85°	0	1
90°	0	



TEST NUMBER: P204288

CATALOG NUMBER: LSR6B30D010BZ EC6B30509050 6LBSWH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1608.3
2.5°	1602.4
5°	1584.7
7.5°	1546.4
10°	1496.2
12.5°	1437.2
15°	1372.3
17.5°	1298.5
20°	1233.6
22.5°	1159.8
25°	1091.9
27.5°	1024.0
30°	959.1
32.5°	903.0
35°	849.9
37.5°	796.8
40°	746.6
42.5°	696.5
45°	646.3
47.5°	590.2
50°	534.1
52.5°	478.1
55°	422.0
57.5°	363.0
60°	306.9
62.5°	253.8
65°	203.6
67.5°	156.4
70°	115.1
72.5°	79.7
75°	47.2
77.5°	20.7
80°	5.9
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)