

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P204978

Luminaire Tested: **LE_6B15D010 EC6B10208040 6LBCS1MMS**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204978
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B15D010 EC6B10208040 6LBCS1MMS
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH CAST MATTE METALLIC SILVER TRIM
WATTAGE D010TR-14.39 W DE010-14.29 W D5LT-14.34 W DMX-14.46 W DL2-15.8 W
DL3-15.28 W DLE-15.432 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1952.6 lumens
Efficiency: N/A
Efficacy: 136.5 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.27
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204978

CATALOG NUMBER: LE_6B15D010 EC6B10208040 6LBCS1MMS

Luminous Intensity Polar Plot





TEST NUMBER: P204978

CATALOG NUMBER: LE_6B15D010 EC6B10208040 6LBCS1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	111	107	103	100	108	105	101	98	100	98	95	97	94	92	93	91	90	88	88	88	88
2	102	95	89	84	100	93	88	83	90	85	81	86	83	79	83	80	78	76	76	76	76
3	94	85	77	72	92	83	76	71	80	74	70	77	73	69	75	71	67	65	65	65	65
4	87	76	68	62	84	74	67	61	72	66	61	70	64	60	68	63	59	57	57	57	57
5	80	68	60	54	78	67	59	54	65	58	53	63	57	53	61	56	52	50	50	50	50
6	74	62	54	48	72	61	53	47	59	52	47	58	51	47	56	51	46	44	44	44	44
7	69	56	48	42	67	56	48	42	54	47	42	53	46	42	51	46	41	40	40	40	40
8	64	52	44	38	63	51	43	38	50	43	38	48	42	38	47	42	37	36	36	36	36
9	60	48	40	35	59	47	40	34	46	39	34	45	39	34	44	38	34	32	32	32	32
10	57	44	36	31	55	43	36	31	43	36	31	42	35	31	41	35	31	29	29	29	29

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204978

CATALOG NUMBER: LE_6B15D010 EC6B10208040 6LBCS1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	84.5	4.3
10°-20°	237.1	12.1
20°-30°	346.3	17.7
30°-40°	396.1	20.3
40°-50°	380.7	19.5
50°-60°	294.0	15.1
60°-70°	164.1	8.4
70°-80°	47.7	2.4
80°-90°	2.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	668.0	34.2
0°-40°	1064.1	54.5
0°-60°	1738.8	89.0
0°-90°	1952.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1952.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	897	
5°	889	85
15°	841	237
25°	753	346
35°	634	396
45°	496	381
55°	330	294
65°	164	164
75°	42	48
85°	1	2
90°	0	



TEST NUMBER: P204978

CATALOG NUMBER: LE_6B15D010 EC6B10208040 6LBCS1MMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	896.8
2.5°	896.8
5°	889.1
7.5°	885.4
10°	872.8
12.5°	857.5
15°	841.1
17.5°	824.8
20°	800.8
22.5°	781.8
25°	752.8
27.5°	723.6
30°	694.6
32.5°	665.6
35°	634.0
37.5°	602.4
40°	565.8
42.5°	533.0
45°	496.4
47.5°	454.6
50°	415.5
52.5°	372.6
55°	329.6
57.5°	285.4
60°	243.8
62.5°	202.1
65°	164.1
67.5°	128.9
70°	96.0
72.5°	66.9
75°	41.6
77.5°	21.5
80°	7.6
82.5°	2.5
85°	1.2
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)