

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P202743

Luminaire Tested: **LSR6B30D010BZ EC6B30509050 6LBWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P202743
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR6B30D010BZ EC6B30509050 6LBWH1
Description: PORTFOLIO 6IN CYLINDER
WIDE DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM
WATTAGE D010TR-27.4 W DE010-27.95 W D5LT-27.65 W DMX-27.73 W DL2-29.56 W
DL3-29.67 W DLE-29.73 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2277.9 lumens
Efficiency: N/A
Efficacy: 81.4 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.16
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P202743

CATALOG NUMBER: LSR6B30D010BZ EC6B30509050 6LBWH1

Luminous Intensity Polar Plot





TEST NUMBER: P202743

CATALOG NUMBER: LSR6B30D010BZ EC6B30509050 6LBWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	109	106	103	110	107	104	101	103	100	98	99	97	95	95	94	93	91			
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81			
3	98	90	84	79	96	89	83	78	86	81	77	83	79	76	81	78	75	73			
4	92	82	75	70	90	81	75	70	79	73	69	77	72	68	75	71	67	65			
5	86	75	68	63	84	74	68	63	72	66	62	71	65	61	69	64	61	59			
6	80	69	62	57	78	68	61	56	67	61	56	65	60	56	64	59	55	53			
7	75	64	56	51	73	63	56	51	62	55	51	60	55	51	59	54	50	49			
8	70	59	52	47	69	58	51	47	57	51	46	56	50	46	55	50	46	44			
9	66	55	48	43	65	54	47	43	53	47	43	52	47	42	51	46	42	41			
10	62	51	44	40	61	50	44	39	50	43	39	49	43	39	48	43	39	38			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P202743

CATALOG NUMBER: LSR6B30D010BZ EC6B30509050 6LBWH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	132.7	5.8
10°-20°	376.5	16.5
20°-30°	552.1	24.2
30°-40°	574.6	25.2
40°-50°	397.5	17.5
50°-60°	173.0	7.6
60°-70°	53.1	2.3
70°-80°	16.0	0.7
80°-90°	2.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1061.3	46.6
0°-40°	1635.8	71.8
0°-60°	2206.4	96.9
0°-90°	2277.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2277.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1405	
5°	1399	133
15°	1337	377
25°	1207	552
35°	930	575
45°	514	398
55°	186	173
65°	50	53
75°	15	16
85°	3	2
90°	0	



TEST NUMBER: P202743

CATALOG NUMBER: LSR6B30D010BZ EC6B30509050 6LBWH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1404.9
2.5°	1407.9
5°	1399.0
7.5°	1387.2
10°	1372.5
12.5°	1357.7
15°	1337.1
17.5°	1310.5
20°	1281.0
22.5°	1248.5
25°	1207.2
27.5°	1154.1
30°	1086.2
32.5°	1015.3
35°	929.7
37.5°	835.3
40°	726.1
42.5°	616.9
45°	513.6
47.5°	416.2
50°	330.6
52.5°	250.9
55°	185.9
57.5°	132.8
60°	91.5
62.5°	67.9
65°	50.2
67.5°	38.4
70°	26.6
72.5°	20.7
75°	14.8
77.5°	8.9
80°	5.9
82.5°	3.0
85°	3.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)