

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P202607

Luminaire Tested: **LE_6B15D010 EC6B10208040 6LBMWMH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P202607
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B15D010 EC6B10208040 6LBMWMH1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
MEDIUM DISTRIBUTION WITH WARM HAZE TRIM
WATTAGE D010TR-14.39 W DE010-14.29 W D5LT-14.34 W DMX-14.46 W DL2-15.8 W
DL3-15.28 W DLE-15.432 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1489.4 lumens
Efficiency: N/A
Efficacy: 104.2 lumens/watt
Spacing Criteria (0/90/45): 0.9 / 0.9 / 0.89
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P202607

CATALOG NUMBER: LE_6B15D010 EC6B10208040 6LBMWMH1

Luminous Intensity Polar Plot





TEST NUMBER: P202607

CATALOG NUMBER: LE_6B15D010 EC6B10208040 6LBMWMH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|---|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | | | | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | | | 0 | |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 |
| RCR | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | | | |
| 1 | 113 | 111 | 108 | 106 | 111 | 108 | 106 | 104 | 104 | 103 | 101 | 101 | 99 | 98 | 97 | 96 | 95 | 93 | | | |
| 2 | 108 | 103 | 99 | 95 | 105 | 101 | 97 | 94 | 98 | 95 | 92 | 95 | 92 | 90 | 92 | 90 | 88 | 86 | | | |
| 3 | 102 | 95 | 90 | 86 | 100 | 94 | 89 | 86 | 91 | 88 | 84 | 89 | 86 | 83 | 87 | 84 | 82 | 80 | | | |
| 4 | 97 | 89 | 83 | 79 | 95 | 88 | 83 | 79 | 86 | 81 | 78 | 84 | 80 | 77 | 82 | 79 | 76 | 74 | | | |
| 5 | 92 | 83 | 77 | 73 | 90 | 82 | 77 | 73 | 80 | 76 | 72 | 79 | 75 | 71 | 77 | 74 | 71 | 69 | | | |
| 6 | 87 | 78 | 72 | 67 | 85 | 77 | 71 | 67 | 76 | 71 | 67 | 74 | 70 | 66 | 73 | 69 | 66 | 64 | | | |
| 7 | 83 | 73 | 67 | 63 | 81 | 72 | 67 | 63 | 71 | 66 | 62 | 70 | 65 | 62 | 69 | 65 | 62 | 60 | | | |
| 8 | 78 | 69 | 63 | 58 | 77 | 68 | 62 | 58 | 67 | 62 | 58 | 66 | 61 | 58 | 65 | 61 | 58 | 56 | | | |
| 9 | 75 | 65 | 59 | 55 | 73 | 64 | 59 | 55 | 63 | 58 | 54 | 62 | 58 | 54 | 62 | 57 | 54 | 53 | | | |
| 10 | 71 | 61 | 55 | 51 | 70 | 61 | 55 | 51 | 60 | 55 | 51 | 59 | 54 | 51 | 58 | 54 | 51 | 50 | | | |

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P202607

CATALOG NUMBER: LE_6B15D010 EC6B10208040 6LBMWMH1

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 152.0 | 10.2 |
| 10°-20° | 390.2 | 26.2 |
| 20°-30° | 479.3 | 32.2 |
| 30°-40° | 328.7 | 22.1 |
| 40°-50° | 105.7 | 7.1 |
| 50°-60° | 21.4 | 1.4 |
| 60°-70° | 8.4 | 0.6 |
| 70°-80° | 3.1 | 0.2 |
| 80°-90° | 0.5 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 1021.6 | 68.6 |
| 0°-40° | 1350.3 | 90.7 |
| 0°-60° | 1477.4 | 99.2 |
| 0°-90° | 1489.4 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 1489.4 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|------|------|
| 0° | 1656 | |
| 5° | 1625 | 152 |
| 15° | 1396 | 390 |
| 25° | 1058 | 479 |
| 35° | 524 | 329 |
| 45° | 125 | 106 |
| 55° | 22 | 21 |
| 65° | 9 | 8 |
| 75° | 2 | 3 |
| 85° | 0 | 0 |
| 90° | 0 | |



TEST NUMBER: P202607

CATALOG NUMBER: LE_6B15D010 EC6B10208040 6LBMWMH1

CANDELA DISTRIBUTION (FULL):

| 0° | |
|-------|--------|
| 0° | 1656.4 |
| 2.5° | 1646.2 |
| 5° | 1624.8 |
| 7.5° | 1584.4 |
| 10° | 1530.0 |
| 12.5° | 1463.0 |
| 15° | 1396.1 |
| 17.5° | 1321.5 |
| 20° | 1239.4 |
| 22.5° | 1153.5 |
| 25° | 1057.5 |
| 27.5° | 951.4 |
| 30° | 817.5 |
| 32.5° | 669.6 |
| 35° | 524.4 |
| 37.5° | 391.6 |
| 40° | 281.8 |
| 42.5° | 192.0 |
| 45° | 125.1 |
| 47.5° | 77.1 |
| 50° | 46.8 |
| 52.5° | 29.0 |
| 55° | 21.5 |
| 57.5° | 16.4 |
| 60° | 12.6 |
| 62.5° | 10.1 |
| 65° | 8.9 |
| 67.5° | 6.4 |
| 70° | 5.0 |
| 72.5° | 3.8 |
| 75° | 2.5 |
| 77.5° | 2.5 |
| 80° | 1.2 |
| 82.5° | 1.2 |
| 85° | 0.0 |
| 87.5° | 0.0 |
| 90° | 0.0 |



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)