

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P203266

Luminaire Tested: **LSR6B40D010BZ EC6B30509024 6LBMH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203266
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR6B40D010BZ EC6B30509024 6LBMH1
Description: PORTFOLIO 6IN CYLINDER
MEDIUM DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM
WATTAGE D010TR-43.02 W DE010-42.54 W D5LT-42.539 W DMX-41.87 W DL2-41.57
W DL3-44.71 W DLE-39.33 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2206.7 lumens
Efficiency: N/A
Efficacy: 52.8 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.93
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 41.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203266

CATALOG NUMBER: LSR6B40D010BZ EC6B30509024 6LBMH1

Luminous Intensity Polar Plot





TEST NUMBER: P203266

CATALOG NUMBER: LSR6B40D010BZ EC6B30509024 6LBMH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20																	
RC	80									70									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																								
RCR																																																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																																				
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	92																																				
2	107	102	97	93	105	100	96	92	97	93	90	94	91	88	91	89	87	85																																				
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78																																				
4	95	87	81	76	93	86	80	76	84	79	75	82	78	74	80	76	73	72																																				
5	90	81	75	70	88	80	74	70	78	73	69	76	72	68	75	71	68	66																																				
6	85	75	69	64	83	75	69	64	73	68	64	72	67	63	70	66	63	61																																				
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																																				
8	76	66	60	55	75	65	59	55	64	59	55	63	58	55	62	58	54	53																																				
9	72	62	56	51	71	61	55	51	60	55	51	60	55	51	59	54	51	49																																				
10	69	58	52	48	68	58	52	48	57	52	48	56	51	48	55	51	48	46																																				

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203266

CATALOG NUMBER: LSR6B40D010BZ EC6B30509024 6LBMH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	199.7	9.0
10°-20°	516.5	23.4
20°-30°	669.3	30.3
30°-40°	496.9	22.5
40°-50°	209.8	9.5
50°-60°	74.5	3.4
60°-70°	28.8	1.3
70°-80°	10.0	0.5
80°-90°	1.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1385.5	62.8
0°-40°	1882.4	85.3
0°-60°	2166.7	98.2
0°-90°	2206.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2206.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2184	
5°	2136	200
15°	1843	517
25°	1484	669
35°	788	497
45°	258	210
55°	79	75
65°	28	29
75°	10	10
85°	0	1
90°	0	



TEST NUMBER: P203266

CATALOG NUMBER: LSR6B40D010BZ EC6B30509024 6LBMH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	2183.7
2.5°	2177.4
5°	2136.5
7.5°	2076.6
10°	2004.1
12.5°	1925.3
15°	1843.4
17.5°	1752.0
20°	1670.1
22.5°	1585.0
25°	1484.2
27.5°	1345.5
30°	1181.7
32.5°	989.4
35°	787.8
37.5°	617.6
40°	469.5
42.5°	349.8
45°	258.4
47.5°	189.1
50°	138.6
52.5°	104.0
55°	78.8
57.5°	59.9
60°	47.3
62.5°	34.7
65°	28.4
67.5°	22.1
70°	15.8
72.5°	12.6
75°	9.5
77.5°	6.3
80°	3.2
82.5°	3.2
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)