

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P204158

Luminaire Tested: **LE_6B15D010 EC6B10209040 6LBSH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204158
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B15D010 EC6B10209040 6LBSH1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM
WATTAGE D010TR-14.39 W DE010-14.29 W D5LT-14.34 W DMX-14.46 W DL2-15.8 W
DL3-15.28 W DLE-15.432 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1656.6 lumens
Efficiency: N/A
Efficacy: 115.8 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.17
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct

Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204158
CATALOG NUMBER: LE_6B15D010 EC6B10209040 6LBSH1

Luminous Intensity Polar Plot





TEST NUMBER: P204158

CATALOG NUMBER: LE_6B15D010 EC6B10209040 6LBSH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88			
2	102	96	90	85	100	94	88	84	90	86	82	87	83	80	84	81	79	77			
3	95	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67			
4	87	77	69	63	85	75	68	63	73	67	62	71	65	61	69	64	60	58			
5	81	69	61	55	79	68	61	55	66	60	55	64	59	54	63	58	53	51			
6	75	63	55	49	73	62	54	49	60	54	49	59	53	48	57	52	48	46			
7	70	58	50	44	68	57	49	44	55	49	44	54	48	43	53	47	43	41			
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37			
9	61	49	41	36	60	48	41	36	47	40	36	46	40	36	45	40	35	34			
10	58	45	38	33	56	45	38	33	44	37	33	43	37	33	42	37	33	31			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204158

CATALOG NUMBER: LE_6B15D010 EC6B10209040 6LBSH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	81.2	4.9
10°-20°	220.6	13.3
20°-30°	306.3	18.5
30°-40°	334.3	20.2
40°-50°	311.8	18.8
50°-60°	236.7	14.3
60°-70°	129.6	7.8
70°-80°	35.7	2.2
80°-90°	0.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	608.1	36.7
0°-40°	942.3	56.9
0°-60°	1490.9	90.0
0°-90°	1656.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1656.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	866	
5°	859	81
15°	786	221
25°	666	306
35°	534	334
45°	405	312
55°	264	237
65°	130	130
75°	31	36
85°	0	0
90°	0	



TEST NUMBER: P204158

CATALOG NUMBER: LE_6B15D010 EC6B10209040 6LBSH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	866.4
2.5°	866.4
5°	859.1
7.5°	848.1
10°	831.8
12.5°	809.9
15°	786.1
17.5°	756.9
20°	729.6
22.5°	696.8
25°	665.8
27.5°	634.8
30°	600.1
32.5°	567.2
35°	534.4
37.5°	501.6
40°	470.6
42.5°	437.8
45°	404.9
47.5°	372.1
50°	335.6
52.5°	301.0
55°	264.5
57.5°	229.9
60°	195.1
62.5°	160.5
65°	129.5
67.5°	100.4
70°	74.8
72.5°	51.1
75°	31.0
77.5°	14.6
80°	3.6
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)