

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204296

Luminaire Tested: **LSR6B40D010BZ EC6B30509024 6LBSWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204296
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR6B40D010BZ EC6B30509024 6LBSWH1
Description: PORTFOLIO 6IN CYLINDER
SHALLOW DISTRIBUTION WITH WHEAT TRIM
WATTAGE D010TR-43.02 W DE010-42.54 W D5LT-42.539 W DMX-41.87 W DL2-41.57
W DL3-44.71 W DLE-39.33 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3161.2 lumens
Efficiency: N/A
Efficacy: 75.6 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1.08
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 41.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204296

CATALOG NUMBER: LSR6B40D010BZ EC6B30509024 6LBSWH1

Luminous Intensity Polar Plot





TEST NUMBER: P204296

CATALOG NUMBER: LSR6B40D010BZ EC6B30509024 6LBSWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	94	92	90	89																			
2	103	96	90	85	100	94	89	84	91	86	83	87	84	81	85	82	79	77																			
3	95	86	79	73	93	84	78	73	82	76	72	79	74	70	76	73	69	67																			
4	88	77	70	64	86	76	69	63	74	68	63	72	66	62	69	65	61	59																			
5	81	70	62	56	79	69	62	56	67	60	55	65	59	55	63	58	54	52																			
6	76	64	56	50	74	63	55	50	61	54	49	60	54	49	58	53	49	47																			
7	71	58	51	45	69	58	50	45	56	49	45	55	49	44	54	48	44	42																			
8	66	54	46	41	65	53	46	41	52	45	40	51	45	40	50	44	40	38																			
9	62	50	42	37	61	49	42	37	48	41	37	47	41	37	46	41	37	35																			
10	58	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32																			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204296

CATALOG NUMBER: LSR6B40D010BZ EC6B30509024 6LBSWH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	173.9	5.5
10°-20°	450.1	14.2
20°-30°	588.7	18.6
30°-40°	623.4	19.7
40°-50°	581.4	18.4
50°-60°	440.4	13.9
60°-70°	238.5	7.5
70°-80°	64.0	2.0
80°-90°	0.9	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1212.7	38.4
0°-40°	1836.0	58.1
0°-60°	2857.8	90.4
0°-90°	3161.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3161.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1885	
5°	1858	174
15°	1609	450
25°	1280	589
35°	996	623
45°	758	581
55°	495	440
65°	239	238
75°	55	64
85°	0	1
90°	0	



TEST NUMBER: P204296

CATALOG NUMBER: LSR6B40D010BZ EC6B30509024 6LBSWH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1885.3
2.5°	1878.4
5°	1857.7
7.5°	1812.7
10°	1753.9
12.5°	1684.7
15°	1608.6
17.5°	1522.1
20°	1446.0
22.5°	1359.5
25°	1279.9
27.5°	1200.4
30°	1124.3
32.5°	1058.6
35°	996.3
37.5°	934.0
40°	875.2
42.5°	816.4
45°	757.6
47.5°	691.9
50°	626.1
52.5°	560.4
55°	494.7
57.5°	425.5
60°	359.8
62.5°	297.5
65°	238.7
67.5°	183.3
70°	134.9
72.5°	93.4
75°	55.3
77.5°	24.2
80°	6.9
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)