

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P203158

Luminaire Tested: **LSR6B40D010BZ EC6B30508027 6LBWMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203158
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR6B40D010BZ EC6B30508027 6LBWMW1
Description: PORTFOLIO 6IN CYLINDER
WIDE DISTRIBUTION WITH MATTE WHITE TRIM
WATTAGE D010TR-43.02 W DE010-42.54 W D5LT-42.539 W DMX-41.87 W DL2-41.57
W DL3-44.71 W DLE-39.33 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3777.3 lumens
Efficiency: N/A
Efficacy: 90.4 lumens/watt
Spacing Criteria (0/90/45): 1.13 / 1.13 / 1.15
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 41.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203158

CATALOG NUMBER: LSR6B40D010BZ EC6B30508027 6LBWMW1

Luminous Intensity Polar Plot





TEST NUMBER: P203158

CATALOG NUMBER: LSR6B40D010BZ EC6B30508027 6LBWMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	107	104	100	108	105	102	99	101	98	96	97	95	93	93	92	90	88			88
2	103	96	90	86	100	94	89	85	91	86	83	88	84	81	85	82	79	77			77
3	95	86	80	74	93	85	79	74	82	77	72	80	75	71	77	73	70	68			68
4	89	78	71	65	86	77	70	65	75	69	64	72	67	63	70	66	62	60			60
5	82	71	64	58	80	70	63	58	68	62	57	66	61	56	65	60	56	54			54
6	77	65	57	52	75	64	57	52	63	56	51	61	55	51	60	54	50	49			49
7	72	60	52	47	70	59	52	47	58	51	46	56	50	46	55	50	46	44			44
8	67	55	48	42	66	55	47	42	53	47	42	52	46	42	51	46	42	40			40
9	63	51	44	39	62	51	44	39	50	43	39	49	43	38	48	42	38	37			37
10	60	48	40	36	58	47	40	36	46	40	36	45	40	35	45	39	35	34			34

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203158

CATALOG NUMBER: LSR6B40D010BZ EC6B30508027 6LBWMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	199.8	5.3
10°-20°	560.2	14.8
20°-30°	807.2	21.4
30°-40°	838.1	22.2
40°-50°	619.6	16.4
50°-60°	370.1	9.8
60°-70°	224.9	6.0
70°-80°	123.2	3.3
80°-90°	34.3	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1567.2	41.5
0°-40°	2405.2	63.7
0°-60°	3394.9	89.9
0°-90°	3777.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3777.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2121	
5°	2107	200
15°	1988	560
25°	1759	807
35°	1352	838
45°	797	620
55°	403	370
65°	224	225
75°	114	123
85°	28	34
90°	0	



TEST NUMBER: P203158

CATALOG NUMBER: LSR6B40D010BZ EC6B30508027 6LBWMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	2121.2
2.5°	2121.2
5°	2107.4
7.5°	2089.1
10°	2061.6
12.5°	2029.6
15°	1988.3
17.5°	1942.5
20°	1896.7
22.5°	1832.6
25°	1759.3
27.5°	1681.4
30°	1580.6
32.5°	1479.8
35°	1351.5
37.5°	1218.7
40°	1072.0
42.5°	930.0
45°	797.2
47.5°	678.0
50°	572.7
52.5°	481.0
55°	403.2
57.5°	343.6
60°	293.2
62.5°	256.6
65°	224.5
67.5°	197.0
70°	169.5
72.5°	142.0
75°	114.5
77.5°	91.6
80°	68.7
82.5°	50.4
85°	27.5
87.5°	13.7
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)