

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204814

Luminaire Tested: **LSR6B40D010BZ EC6B30509027 6LBCSMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204814
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR6B40D010BZ EC6B30509027 6LBCSMW1
Description: PORTFOLIO 6IN CYLINDER
SHALLOW DISTRIBUTION WITH CAST MATTE WHITE TRIM
WATTAGE D010TR-43.02 W DE010-42.54 W D5LT-42.539 W DMX-41.87 W DL2-41.57
W DL3-44.71 W DLE-39.33 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3768.9 lumens
Efficiency: N/A
Efficacy: 90.2 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.33
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 41.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204814

CATALOG NUMBER: LSR6B40D010BZ EC6B30509027 6LBCSMW1

Luminous Intensity Polar Plot





TEST NUMBER: P204814

CATALOG NUMBER: LSR6B40D010BZ EC6B30509027 6LBCSMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	110	106	102	99	108	104	100	97	100	97	94	96	93	91	92	90	89	87		
2	101	94	87	82	99	92	86	81	88	84	79	85	81	78	82	79	76	74		
3	93	83	75	70	90	81	74	69	79	73	68	76	71	67	73	69	65	63		
4	85	74	66	60	83	73	65	59	70	64	58	68	62	58	66	61	57	55		
5	79	66	58	52	77	65	57	51	63	56	51	61	55	50	60	54	50	48		
6	73	60	52	45	71	59	51	45	57	50	45	56	49	44	54	49	44	42		
7	68	55	46	40	66	54	46	40	52	45	40	51	44	40	50	44	39	37		
8	63	50	42	36	61	49	41	36	48	41	36	47	40	36	46	40	35	33		
9	59	46	38	33	57	45	38	32	44	37	32	43	37	32	42	36	32	30		
10	55	42	35	30	54	42	34	30	41	34	29	40	34	29	39	33	29	27		

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204814

CATALOG NUMBER: LSR6B40D010BZ EC6B30509027 6LBCSMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	145.8	3.9
10°-20°	415.2	11.0
20°-30°	624.6	16.6
30°-40°	740.2	19.6
40°-50°	736.6	19.5
50°-60°	593.9	15.8
60°-70°	359.2	9.5
70°-80°	133.4	3.5
80°-90°	19.9	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1185.7	31.5
0°-40°	1925.9	51.1
0°-60°	3256.4	86.4
0°-90°	3768.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3768.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1539	
5°	1532	146
15°	1471	415
25°	1357	625
35°	1185	740
45°	959	737
55°	662	594
65°	361	359
75°	121	133
85°	16	20
90°	0	



TEST NUMBER: P204814

CATALOG NUMBER: LSR6B40D010BZ EC6B30509027 6LBCSMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1539.4
2.5°	1539.4
5°	1532.5
7.5°	1527.9
10°	1514.2
12.5°	1491.4
15°	1470.8
17.5°	1448.0
20°	1420.6
22.5°	1393.2
25°	1356.6
27.5°	1317.8
30°	1274.4
32.5°	1233.3
35°	1185.4
37.5°	1135.1
40°	1075.7
42.5°	1018.6
45°	959.2
47.5°	893.0
50°	819.9
52.5°	744.6
55°	662.3
57.5°	589.3
60°	507.0
62.5°	433.9
65°	360.9
67.5°	292.3
70°	228.4
72.5°	171.3
75°	121.0
77.5°	77.7
80°	45.7
82.5°	27.4
85°	16.0
87.5°	6.9
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)