

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P203061

Luminaire Tested: **LSR6B40D010BZ EC6B30509027 6LBWB1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203061
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR6B40D010BZ EC6B30509027 6LBWB1
Description: PORTFOLIO 6IN CYLINDER
WIDE DISTRIBUTION WITH SPECULAR BLACK TRIM
WATTAGE D010TR-43.02 W DE010-42.54 W D5LT-42.539 W DMX-41.87 W DL2-41.57
W DL3-44.71 W DLE-39.33 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1930.3 lumens
Efficiency: N/A
Efficacy: 46.2 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.08 / 1.08
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 41.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203061

CATALOG NUMBER: LSR6B40D010BZ EC6B30509027 6LBWB1

Luminous Intensity Polar Plot





TEST NUMBER: P203061

CATALOG NUMBER: LSR6B40D010BZ EC6B30509027 6LBWB1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20																	
RC	80									70									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																					
RCR																																																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			100																	
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92																			92																	
2	106	101	97	93	104	99	95	92	96	93	90	93	90	88	90	88	86	84																			84																	
3	100	93	87	83	98	92	86	82	89	85	81	86	83	80	84	81	78	77																			77																	
4	94	86	79	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			70																	
5	89	79	73	68	87	78	72	67	76	71	67	75	70	66	73	69	66	64																			64																	
6	83	73	67	62	82	72	66	61	71	65	61	69	64	61	68	64	60	59																			59																	
7	78	68	61	56	77	67	61	56	66	60	56	65	60	56	63	59	55	54																			54																	
8	74	63	57	52	73	63	56	52	61	56	52	60	55	51	59	55	51	50																			50																	
9	70	59	52	48	69	58	52	48	57	52	48	57	51	47	56	51	47	46																			46																	
10	66	55	49	44	65	55	49	44	54	48	44	53	48	44	52	47	44	42																			42																	

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203061

CATALOG NUMBER: LSR6B40D010BZ EC6B30509027 6LBWB1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	136.8	7.1
10°-20°	382.5	19.8
20°-30°	535.8	27.8
30°-40°	511.7	26.5
40°-50°	291.4	15.1
50°-60°	71.2	3.7
60°-70°	0.9	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1055.1	54.7
0°-40°	1566.8	81.2
0°-60°	1929.4	100.0
0°-90°	1930.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1930.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1455	
5°	1443	137
15°	1356	382
25°	1172	536
35°	834	512
45°	374	291
55°	71	71
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P203061

CATALOG NUMBER: LSR6B40D010BZ EC6B30509027 6LBWB1

CANDELA DISTRIBUTION (FULL):

0°	
0°	1454.8
2.5°	1454.8
5°	1443.0
7.5°	1427.3
10°	1415.5
12.5°	1391.9
15°	1356.5
17.5°	1325.1
20°	1285.7
22.5°	1234.6
25°	1171.7
27.5°	1100.9
30°	1022.3
32.5°	927.9
35°	833.6
37.5°	719.5
40°	597.7
42.5°	483.6
45°	373.5
47.5°	275.2
50°	192.7
52.5°	121.9
55°	70.8
57.5°	31.5
60°	7.9
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)