

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P205507

Luminaire Tested: **LE_6B20D010 EC6B10209727 6LBMGPH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P205507
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B20D010 EC6B10209727 6LBMGPH1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
MEDIUM DISTRIBUTION WITH GRAPHITE HAZE TRIM
WATTAGE D010TR-21.86 W DE010-20.46 W D5LT-21.24 W DMX-20.89 W DL2-22.5 W
DL3-21.8 6 W DLE-22.46 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1015.2 lumens
Efficiency: N/A
Efficacy: 48.8 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.91
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 20.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P205507

CATALOG NUMBER: LE_6B20D010 EC6B10209727 6LBMGPH1

Luminous Intensity Polar Plot





TEST NUMBER: P205507

CATALOG NUMBER: LE_6B20D010 EC6B10209727 6LBMGPH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	108	105	111	108	106	104	104	102	101	100	99	98	97	96	95	93																			
2	107	102	98	94	105	100	97	93	97	94	91	94	92	89	91	89	87	86																			
3	102	95	90	85	100	93	89	85	91	87	83	88	85	82	86	83	81	79																			
4	96	88	82	78	94	87	82	77	85	80	77	83	79	76	81	78	75	73																			
5	91	82	76	72	89	81	76	71	79	74	71	78	73	70	76	72	69	68																			
6	86	77	71	66	85	76	70	66	74	69	65	73	68	65	72	68	64	63																			
7	82	72	66	61	80	71	65	61	70	65	61	69	64	60	68	63	60	59																			
8	77	68	61	57	76	67	61	57	66	60	57	65	60	56	64	59	56	55																			
9	74	64	57	53	72	63	57	53	62	57	53	61	56	53	60	56	53	51																			
10	70	60	54	50	69	59	54	50	59	53	50	58	53	49	57	53	49	48																			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P205507

CATALOG NUMBER: LE_6B20D010 EC6B10209727 6LBMGPH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	97.2	9.6
10°-20°	252.2	24.8
20°-30°	321.3	31.6
30°-40°	227.1	22.4
40°-50°	82.9	8.2
50°-60°	23.0	2.3
60°-70°	8.3	0.8
70°-80°	2.9	0.3
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	670.7	66.1
0°-40°	897.8	88.4
0°-60°	1003.7	98.9
0°-90°	1015.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1015.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1058	
5°	1040	97
15°	898	252
25°	714	321
35°	361	227
45°	100	83
55°	25	23
65°	8	8
75°	2	3
85°	0	0
90°	0	



TEST NUMBER: P205507

CATALOG NUMBER: LE_6B20D010 EC6B10209727 6LBMGPH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1057.9
2.5°	1053.9
5°	1039.5
7.5°	1010.8
10°	980.0
12.5°	939.0
15°	898.0
17.5°	857.0
20°	816.0
22.5°	766.8
25°	713.5
27.5°	639.6
30°	557.6
32.5°	459.2
35°	360.9
37.5°	274.8
40°	200.9
42.5°	145.6
45°	100.5
47.5°	67.6
50°	45.1
52.5°	30.8
55°	24.6
57.5°	18.5
60°	14.4
62.5°	10.2
65°	8.2
67.5°	6.1
70°	4.1
72.5°	4.1
75°	2.0
77.5°	2.0
80°	2.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)