

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P202752

Luminaire Tested: **LSR6B40D010BZ EC6B30509027 6LBWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P202752
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR6B40D010BZ EC6B30509027 6LBWH1
Description: PORTFOLIO 6IN CYLINDER
WIDE DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM
WATTAGE D010TR-43.02 W DE010-42.54 W D5LT-42.539 W DMX-41.87 W DL2-41.57
W DL3-44.71 W DLE-39.33 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3035.1 lumens
Efficiency: N/A
Efficacy: 72.6 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.16
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 41.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P202752

CATALOG NUMBER: LSR6B40D010BZ EC6B30509027 6LBWH1

Luminous Intensity Polar Plot





TEST NUMBER: P202752

CATALOG NUMBER: LSR6B40D010BZ EC6B30509027 6LBWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20																	
RC	80									70									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																								
RCR	0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																																			
	1	112	109	106	103	110	107	104	101	103	100	98	99	97	95	95	94	93	91																																			
	2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81																																			
	3	98	90	84	79	96	89	83	78	86	81	77	83	79	76	81	78	75	73																																			
	4	92	82	75	70	90	81	75	70	79	73	69	77	72	68	75	71	67	65																																			
	5	86	75	68	63	84	74	68	63	72	66	62	71	65	61	69	64	61	59																																			
	6	80	69	62	57	78	68	61	56	67	61	56	65	60	56	64	59	55	53																																			
	7	75	64	56	51	73	63	56	51	62	55	51	60	55	51	59	54	50	49																																			
	8	70	59	52	47	69	58	51	47	57	51	46	56	50	46	55	50	46	44																																			
	9	66	55	48	43	65	54	47	43	53	47	43	52	47	42	51	46	42	41																																			
	10	62	51	44	40	61	50	44	39	50	43	39	49	43	39	48	43	39	38																																			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P202752

CATALOG NUMBER: LSR6B40D010BZ EC6B30509027 6LBWH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	176.8	5.8
10°-20°	501.7	16.5
20°-30°	735.6	24.2
30°-40°	765.6	25.2
40°-50°	529.7	17.5
50°-60°	230.6	7.6
60°-70°	70.7	2.3
70°-80°	21.2	0.7
80°-90°	3.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1414.1	46.6
0°-40°	2179.7	71.8
0°-60°	2940.0	96.9
0°-90°	3035.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3035.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1872	
5°	1864	177
15°	1782	502
25°	1608	736
35°	1239	766
45°	684	530
55°	248	231
65°	67	71
75°	20	21
85°	4	3
90°	0	



TEST NUMBER: P202752

CATALOG NUMBER: LSR6B40D010BZ EC6B30509027 6LBWH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1872.0
2.5°	1875.9
5°	1864.1
7.5°	1848.4
10°	1828.7
12.5°	1809.1
15°	1781.6
17.5°	1746.2
20°	1706.8
22.5°	1663.6
25°	1608.5
27.5°	1537.7
30°	1447.3
32.5°	1352.9
35°	1238.8
37.5°	1113.0
40°	967.5
42.5°	822.0
45°	684.3
47.5°	554.5
50°	440.5
52.5°	334.3
55°	247.8
57.5°	177.0
60°	121.9
62.5°	90.5
65°	66.9
67.5°	51.1
70°	35.4
72.5°	27.5
75°	19.7
77.5°	11.8
80°	7.9
82.5°	3.9
85°	3.9
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)