

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204809

Luminaire Tested: **LSR6B40D010BZ EC6B30508030 6LBCSMW1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P204809  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LSR6B40D010BZ EC6B30508030 6LBCSMW1  
Description: PORTFOLIO 6IN CYLINDER  
SHALLOW DISTRIBUTION WITH CAST MATTE WHITE TRIM  
WATTAGE D010TR-43.02 W DE010-42.54 W D5LT-42.539 W DMX-41.87 W DL2-41.57  
W DL3-44.71 W DLE-39.33 W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4588.5 lumens  
Efficiency: N/A  
Efficacy: 109.8 lumens/watt  
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.33  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 41.8  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P204809

CATALOG NUMBER: LSR6B40D010BZ EC6B30508030 6LBCSMW1

### Luminous Intensity Polar Plot





TEST NUMBER: P204809

CATALOG NUMBER: LSR6B40D010BZ EC6B30508030 6LBCSMW1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	110	106	102	99	108	104	100	97	100	97	94	96	93	91	92	90	89	87			87
2	101	94	87	82	99	92	86	81	88	84	79	85	81	78	82	79	76	74			74
3	93	83	75	70	90	81	74	69	79	73	68	76	71	67	73	69	65	63			63
4	85	74	66	60	83	73	65	59	70	64	58	68	62	58	66	61	57	55			55
5	79	66	58	52	77	65	57	51	63	56	51	61	55	50	60	54	50	48			48
6	73	60	52	45	71	59	51	45	57	50	45	56	49	44	54	49	44	42			42
7	68	55	46	40	66	54	46	40	52	45	40	51	44	40	50	44	39	37			37
8	63	50	42	36	61	49	41	36	48	41	36	47	40	36	46	40	35	33			33
9	59	46	38	33	57	45	38	32	44	37	32	43	37	32	42	36	32	30			30
10	55	42	35	30	54	42	34	30	41	34	29	40	34	29	39	33	29	27			27

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P204809

CATALOG NUMBER: LSR6B40D010BZ EC6B30508030 6LBCSMW1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	177.6	3.9
10°-20°	505.5	11.0
20°-30°	760.5	16.6
30°-40°	901.2	19.6
40°-50°	896.8	19.5
50°-60°	723.0	15.8
60°-70°	437.4	9.5
70°-80°	162.4	3.5
80°-90°	24.2	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1443.5	31.5
0°-40°	2344.7	51.1
0°-60°	3964.6	86.4
0°-90°	4588.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4588.5	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1874	
5°	1866	178
15°	1791	506
25°	1652	760
35°	1443	901
45°	1168	897
55°	806	723
65°	439	437
75°	147	162
85°	20	24
90°	0	



TEST NUMBER: P204809

CATALOG NUMBER: LSR6B40D010BZ EC6B30508030 6LBCSMW1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1874.1
2.5°	1874.1
5°	1865.8
7.5°	1860.2
10°	1843.5
12.5°	1815.7
15°	1790.7
17.5°	1762.9
20°	1729.5
22.5°	1696.1
25°	1651.7
27.5°	1604.4
30°	1551.6
32.5°	1501.5
35°	1443.1
37.5°	1381.9
40°	1309.6
42.5°	1240.1
45°	1167.8
47.5°	1087.2
50°	998.2
52.5°	906.5
55°	806.4
57.5°	717.4
60°	617.3
62.5°	528.3
65°	439.3
67.5°	355.9
70°	278.1
72.5°	208.5
75°	147.4
77.5°	94.5
80°	55.6
82.5°	33.4
85°	19.5
87.5°	8.3
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)