

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P203442

Luminaire Tested: **LE_6B20D010 EC6B10208030 6LBMB1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203442
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B20D010 EC6B10208030 6LBMB1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
MEDIUM DISTRIBUTION WITH SPECULAR BLACK TRIM
WATTAGE D010TR-21.86 W DE010-20.46 W D5LT-21.24 W DMX-20.89 W DL2-22.5 W
DL3-21.8 6 W DLE-22.46 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1109.2 lumens
Efficiency: N/A
Efficacy: 53.3 lumens/watt
Spacing Criteria (0/90/45): 0.85 / 0.85 / 0.86
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct

Input Watts (W): 20.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT





TEST NUMBER: P203442

CATALOG NUMBER: LE_6B20D010 EC6B10208030 6LBMB1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20																		
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR	0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100	100	100	100	100	100	100	100																	
	1	114	111	109	106	111	109	107	105	105	103	102	101	100	99	98	97	96	94	94	94	94	94	94	94	94	94	94	94																	
	2	108	104	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88	88	88	88	88	88	88	88	88	88	88																	
	3	103	97	92	88	101	95	91	87	93	89	86	90	87	85	88	86	83	82	82	82	82	82	82	82	82	82	82	82																	
	4	98	91	85	81	96	90	85	81	87	83	80	85	82	79	84	81	78	76	76	76	76	76	76	76	76	76	76	76																	
	5	93	85	79	75	92	84	79	75	82	78	74	81	77	74	79	76	73	72	72	72	72	72	72	72	72	72	72	72																	
	6	89	80	74	70	87	79	74	70	78	73	69	76	72	69	75	71	68	67	67	67	67	67	67	67	67	67	67	67																	
	7	84	75	69	65	83	75	69	65	73	68	65	72	68	65	71	67	64	63	63	63	63	63	63	63	63	63	63	63																	
	8	80	71	65	61	79	71	65	61	69	64	61	68	64	61	67	63	60	59	59	59	59	59	59	59	59	59	59	59																	
	9	77	67	61	58	76	67	61	57	66	61	57	65	60	57	64	60	57	56	56	56	56	56	56	56	56	56	56	56																	
	10	73	64	58	54	72	63	58	54	62	57	54	62	57	54	61	57	54	53	53	53	53	53	53	53	53	53	53	53																	

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203442

CATALOG NUMBER: LE_6B20D010 EC6B10208030 6LBMB1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	126.7	11.4
10°-20°	312.6	28.2
20°-30°	376.6	33.9
30°-40°	238.2	21.5
40°-50°	54.5	4.9
50°-60°	0.6	0.1
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	815.8	73.6
0°-40°	1054.0	95.0
0°-60°	1109.2	100.0
0°-90°	1109.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1109.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1396	
5°	1365	127
15°	1115	313
25°	834	377
35°	376	238
45°	60	55
55°	0	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P203442

CATALOG NUMBER: LE_6B20D010 EC6B10208030 6LBMB1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1396.2
2.5°	1390.6
5°	1364.8
7.5°	1316.0
10°	1255.8
12.5°	1184.1
15°	1115.4
17.5°	1049.4
20°	980.6
22.5°	911.8
25°	834.4
27.5°	742.6
30°	630.8
32.5°	504.6
35°	375.6
37.5°	266.6
40°	180.6
42.5°	111.9
45°	60.2
47.5°	25.8
50°	5.8
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)