

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P204266

Luminaire Tested: **LE_6B20D010 EC6B10208030 6LBSWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204266
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B20D010 EC6B10208030 6LBSWH1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH WHEAT TRIM
WATTAGE D010TR-21.86 W DE010-20.46 W D5LT-21.24 W DMX-20.89 W DL2-22.5 W
DL3-21.8 6 W DLE-22.46 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2667.8 lumens
Efficiency: N/A
Efficacy: 128.3 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1.08
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 20.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204266

CATALOG NUMBER: LE_6B20D010 EC6B10208030 6LBSWH1

Luminous Intensity Polar Plot





TEST NUMBER: P204266

CATALOG NUMBER: LE_6B20D010 EC6B10208030 6LBSWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	94	92	90	89																			
2	103	96	90	85	100	94	89	84	91	86	83	87	84	81	85	82	79	77																			
3	95	86	79	73	93	84	78	73	82	76	72	79	74	70	76	73	69	67																			
4	88	77	70	64	86	76	69	63	74	68	63	72	66	62	69	65	61	59																			
5	81	70	62	56	79	69	62	56	67	60	55	65	59	55	63	58	54	52																			
6	76	64	56	50	74	63	55	50	61	54	49	60	54	49	58	53	49	47																			
7	71	58	51	45	69	58	50	45	56	49	45	55	49	44	54	48	44	42																			
8	66	54	46	41	65	53	46	41	52	45	40	51	45	40	50	44	40	38																			
9	62	50	42	37	61	49	42	37	48	41	37	47	41	37	46	41	37	35																			
10	58	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32																			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204266

CATALOG NUMBER: LE_6B20D010 EC6B10208030 6LBSWH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	146.7	5.5
10°-20°	379.8	14.2
20°-30°	496.8	18.6
30°-40°	526.0	19.7
40°-50°	490.7	18.4
50°-60°	371.6	13.9
60°-70°	201.3	7.5
70°-80°	54.0	2.0
80°-90°	0.8	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1023.4	38.4
0°-40°	1549.4	58.1
0°-60°	2411.7	90.4
0°-90°	2667.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2667.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1591	
5°	1568	147
15°	1358	380
25°	1080	497
35°	841	526
45°	639	491
55°	418	372
65°	201	201
75°	47	54
85°	0	1
90°	0	



TEST NUMBER: P204266

CATALOG NUMBER: LE_6B20D010 EC6B10208030 6LBSWH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1591.0
2.5°	1585.1
5°	1567.6
7.5°	1529.8
10°	1480.1
12.5°	1421.8
15°	1357.5
17.5°	1284.5
20°	1220.2
22.5°	1147.2
25°	1080.1
27.5°	1013.0
30°	948.8
32.5°	893.2
35°	840.8
37.5°	788.2
40°	738.6
42.5°	689.0
45°	639.4
47.5°	583.9
50°	528.4
52.5°	472.9
55°	417.5
57.5°	359.1
60°	303.6
62.5°	251.0
65°	201.4
67.5°	154.8
70°	113.9
72.5°	78.9
75°	46.8
77.5°	20.4
80°	5.9
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)