

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P202721

Luminaire Tested: **LE\_6B20D010 EC6B10208030 6LBWH1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P202721  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LE\_6B20D010 EC6B10208030 6LBWH1  
Description: PORTFOLIO 6 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT  
WIDE DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM  
WATTAGE D010TR-21.86 W DE010-20.46 W D5LT-21.24 W DMX-20.89 W DL2-22.5 W  
DL3-21.8 6 W DLE-22.46 W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2253.2 lumens  
Efficiency: N/A  
Efficacy: 108.3 lumens/watt  
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.16  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 20.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P202721

CATALOG NUMBER: LE\_6B20D010 EC6B10208030 6LBWH1

### Luminous Intensity Polar Plot





TEST NUMBER: P202721

CATALOG NUMBER: LE\_6B20D010 EC6B10208030 6LBWH1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	109	106	103	110	107	104	101	103	100	98	99	97	95	95	94	93	91			
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81			
3	98	90	84	79	96	89	83	78	86	81	77	83	79	76	81	78	75	73			
4	92	82	75	70	90	81	75	70	79	73	69	77	72	68	75	71	67	65			
5	86	75	68	63	84	74	68	63	72	66	62	71	65	61	69	64	61	59			
6	80	69	62	57	78	68	61	56	67	61	56	65	60	56	64	59	55	53			
7	75	64	56	51	73	63	56	51	62	55	51	60	55	51	59	54	50	49			
8	70	59	52	47	69	58	51	47	57	51	46	56	50	46	55	50	46	44			
9	66	55	48	43	65	54	47	43	53	47	43	52	47	42	51	46	42	41			
10	62	51	44	40	61	50	44	39	50	43	39	49	43	39	48	43	39	38			

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P202721

CATALOG NUMBER: LE\_6B20D010 EC6B10208030 6LBWH1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	131.3	5.8
10°-20°	372.5	16.5
20°-30°	546.1	24.2
30°-40°	568.4	25.2
40°-50°	393.2	17.5
50°-60°	171.2	7.6
60°-70°	52.5	2.3
70°-80°	15.8	0.7
80°-90°	2.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1049.8	46.6
0°-40°	1618.2	71.8
0°-60°	2182.6	96.9
0°-90°	2253.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2253.2	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1390	
5°	1384	131
15°	1323	372
25°	1194	546
35°	920	568
45°	508	393
55°	184	171
65°	50	52
75°	15	16
85°	3	2
90°	0	



TEST NUMBER: P202721

CATALOG NUMBER: LE\_6B20D010 EC6B10208030 6LBWH1

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1389.8
2.5°	1392.8
5°	1384.0
7.5°	1372.2
10°	1357.6
12.5°	1343.1
15°	1322.6
17.5°	1296.4
20°	1267.1
22.5°	1235.0
25°	1194.1
27.5°	1141.6
30°	1074.5
32.5°	1004.4
35°	919.8
37.5°	826.2
40°	718.2
42.5°	610.2
45°	508.0
47.5°	411.6
50°	327.0
52.5°	248.1
55°	184.0
57.5°	131.4
60°	90.5
62.5°	67.1
65°	49.6
67.5°	38.0
70°	26.2
72.5°	20.5
75°	14.6
77.5°	8.8
80°	5.9
82.5°	2.9
85°	2.9
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)