

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P205217

Luminaire Tested: **LSR6B40D010BZ EC6B30508030 6LBWLI1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P205217
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR6B40D010BZ EC6B30508030 6LBWL1
Description: PORTFOLIO 6IN CYLINDER
WIDE DISTRIBUTION WITH SPECULAR CLEAR TRIM
WATTAGE D010TR-43.02 W DE010-42.54 W D5LT-42.539 W DMX-41.87 W DL2-41.57
W DL3-44.71 W DLE-39.33 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4221.6 lumens
Efficiency: N/A
Efficacy: 101.0 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.18
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 41.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P205217

CATALOG NUMBER: LSR6B40D010BZ EC6B30508030 6LBWLI1

Luminous Intensity Polar Plot





TEST NUMBER: P205217

CATALOG NUMBER: LSR6B40D010BZ EC6B30508030 6LBWLI1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20																	
RC	80									70									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																								
RCR																																																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																																				
1	113	110	107	104	110	107	105	103	103	101	99	100	98	97	96	95	94	92																																				
2	106	101	96	92	104	99	95	91	95	92	89	92	90	87	90	87	85	83																																				
3	100	92	87	82	97	91	86	81	88	84	80	86	82	79	83	80	77	76																																				
4	93	85	78	73	92	84	78	73	81	76	72	79	75	71	77	74	70	69																																				
5	88	78	71	66	86	77	71	66	75	70	65	73	69	65	72	68	64	63																																				
6	82	72	65	60	81	71	65	60	70	64	59	68	63	59	67	62	59	57																																				
7	77	67	60	55	76	66	59	55	65	59	54	63	58	54	62	57	54	52																																				
8	73	62	55	50	71	61	55	50	60	54	50	59	54	50	58	53	49	48																																				
9	69	57	51	46	67	57	50	46	56	50	46	55	50	46	54	49	46	44																																				
10	65	54	47	43	64	53	47	42	52	46	42	51	46	42	51	46	42	41																																				

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P205217

CATALOG NUMBER: LSR6B40D010BZ EC6B30508030 6LBWLI1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	254.4	6.0
10°-20°	764.7	18.1
20°-30°	1152.8	27.3
30°-40°	1179.9	27.9
40°-50°	687.4	16.3
50°-60°	158.0	3.7
60°-70°	19.4	0.5
70°-80°	5.1	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2171.9	51.4
0°-40°	3351.8	79.4
0°-60°	4197.1	99.4
0°-90°	4221.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4221.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2637	
5°	2652	254
15°	2709	765
25°	2527	1153
35°	1914	1180
45°	886	687
55°	153	158
65°	14	19
75°	5	5
85°	0	0
90°	0	



TEST NUMBER: P205217

CATALOG NUMBER: LSR6B40D010BZ EC6B30508030 6LBWLI1

CANDELA DISTRIBUTION (FULL):

	0°
0°	2637.3
2.5°	2632.5
5°	2651.6
7.5°	2670.8
10°	2694.7
12.5°	2699.5
15°	2709.1
17.5°	2699.5
20°	2675.6
22.5°	2599.0
25°	2527.2
27.5°	2412.3
30°	2263.9
32.5°	2110.8
35°	1914.5
37.5°	1694.4
40°	1450.3
42.5°	1177.4
45°	885.5
47.5°	617.4
50°	406.8
52.5°	258.5
55°	153.2
57.5°	81.4
60°	43.1
62.5°	23.9
65°	14.4
67.5°	14.4
70°	9.6
72.5°	4.8
75°	4.8
77.5°	4.8
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)