

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P205121

Luminaire Tested: **LSR6B40D010BZ EC6B30509030 6LBMLI1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P205121  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LSR6B40D010BZ EC6B30509030 6LBMLI1  
Description: PORTFOLIO 6IN CYLINDER  
MEDIUM DISTRIBUTION WITH SPECULAR CLEAR TRIM  
WATTAGE D010TR-43.02 W DE010-42.54 W D5LT-42.539 W DMX-41.87 W DL2-41.57  
W DL3-44.71 W DLE-39.33 W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3192.5 lumens  
Efficiency: N/A  
Efficacy: 76.4 lumens/watt  
Spacing Criteria (0/90/45): 0.85 / 0.85 / 0.85  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 41.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P205121

CATALOG NUMBER: LSR6B40D010BZ EC6B30509030 6LBML11

### Luminous Intensity Polar Plot





TEST NUMBER: P205121

CATALOG NUMBER: LSR6B40D010BZ EC6B30509030 6LBML11

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									20																	
RC	80									70									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																								
RCR																																																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																																				
1	114	111	109	106	111	109	107	105	105	103	101	101	100	98	98	97	96	94																																				
2	108	103	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88																																				
3	103	97	92	88	101	95	91	87	93	89	86	90	87	85	88	85	83	82																																				
4	98	91	85	81	96	89	84	81	87	83	80	85	82	79	83	80	78	76																																				
5	93	85	79	75	91	84	79	75	82	78	74	81	77	73	79	76	73	71																																				
6	89	80	74	70	87	79	74	70	78	73	69	76	72	69	75	71	68	67																																				
7	84	75	69	65	83	75	69	65	73	68	65	72	68	64	71	67	64	63																																				
8	80	71	65	61	79	70	65	61	69	64	61	68	64	60	67	63	60	59																																				
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55																																				
10	73	64	58	54	72	63	58	54	62	57	54	62	57	54	61	57	54	52																																				

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P205121

CATALOG NUMBER: LSR6B40D010BZ EC6B30509030 6LBMLI1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	368.0	11.5
10°-20°	916.3	28.7
20°-30°	1065.2	33.4
30°-40°	652.3	20.4
40°-50°	162.0	5.1
50°-60°	18.9	0.6
60°-70°	7.1	0.2
70°-80°	2.7	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2349.5	73.6
0°-40°	3001.8	94.0
0°-60°	3182.7	99.7
0°-90°	3192.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3192.5	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3995	
5°	3942	368
15°	3288	916
25°	2357	1065
35°	1021	652
45°	180	162
55°	16	19
65°	8	7
75°	4	3
85°	0	0
90°	0	



TEST NUMBER: P205121

CATALOG NUMBER: LSR6B40D010BZ EC6B30509030 6LBML11

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	3995.2
2.5°	3991.1
5°	3942.1
7.5°	3835.9
10°	3692.9
12.5°	3505.0
15°	3288.5
17.5°	3055.6
20°	2826.9
22.5°	2598.1
25°	2357.1
27.5°	2079.3
30°	1760.7
32.5°	1388.9
35°	1021.3
37.5°	719.0
40°	490.2
42.5°	306.4
45°	179.7
47.5°	102.1
50°	53.1
52.5°	24.5
55°	16.3
57.5°	12.3
60°	12.3
62.5°	8.2
65°	8.2
67.5°	4.1
70°	4.1
72.5°	4.1
75°	4.1
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)