

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P205000

Luminaire Tested: **LE\_6B20D010 EC6B10209730 6LBCS1MMS**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P205000  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LE\_6B20D010 EC6B10209730 6LBCS1MMS  
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT  
SHALLOW DISTRIBUTION WITH CAST MATTE METALLIC SILVER TRIM  
WATTAGE D010TR-21.86 W DE010-20.46 W D5LT-21.24 W DMX-20.89 W DL2-22.5 W  
DL3-21.8 6 W DLE-22.46 W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1955.8 lumens  
Efficiency: N/A  
Efficacy: 94.0 lumens/watt  
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.27  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 20.8  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P205000

CATALOG NUMBER: LE\_6B20D010 EC6B10209730 6LBCS1MMS

### Luminous Intensity Polar Plot





TEST NUMBER: P205000

CATALOG NUMBER: LE\_6B20D010 EC6B10209730 6LBCS1MMS

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	111	107	103	100	108	105	101	98	100	98	95	97	94	92	93	91	90	88																			
2	102	95	89	84	100	93	88	83	90	85	81	86	83	79	83	80	78	76																			
3	94	85	77	72	92	83	76	71	80	74	70	77	73	69	75	71	67	65																			
4	87	76	68	62	84	74	67	61	72	66	61	70	64	60	68	63	59	57																			
5	80	68	60	54	78	67	59	54	65	58	53	63	57	53	61	56	52	50																			
6	74	62	54	48	72	61	53	47	59	52	47	58	51	47	56	51	46	44																			
7	69	56	48	42	67	56	48	42	54	47	42	53	46	42	51	46	41	40																			
8	64	52	44	38	63	51	43	38	50	43	38	48	42	38	47	42	37	36																			
9	60	48	40	35	59	47	40	34	46	39	34	45	39	34	44	38	34	32																			
10	57	44	36	31	55	43	36	31	43	36	31	42	35	31	41	35	31	29																			

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P205000

CATALOG NUMBER: LE\_6B20D010 EC6B10209730 6LBCS1MMS

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	84.6	4.3
10°-20°	237.5	12.1
20°-30°	346.9	17.7
30°-40°	396.8	20.3
40°-50°	381.3	19.5
50°-60°	294.4	15.1
60°-70°	164.3	8.4
70°-80°	47.8	2.4
80°-90°	2.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	669.1	34.2
0°-40°	1065.8	54.5
0°-60°	1741.6	89.0
0°-90°	1955.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1955.8	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	898	
5°	891	85
15°	842	238
25°	754	347
35°	635	397
45°	497	381
55°	330	294
65°	164	164
75°	42	48
85°	1	2
90°	0	



TEST NUMBER: P205000

CATALOG NUMBER: LE\_6B20D010 EC6B10209730 6LBCS1MMS

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	898.1
2.5°	898.1
5°	890.6
7.5°	886.8
10°	874.1
12.5°	859.0
15°	842.5
17.5°	826.1
20°	802.0
22.5°	783.1
25°	754.0
27.5°	724.9
30°	695.8
32.5°	666.6
35°	635.0
37.5°	603.4
40°	566.8
42.5°	533.9
45°	497.1
47.5°	455.4
50°	416.2
52.5°	373.2
55°	330.1
57.5°	285.9
60°	244.1
62.5°	202.4
65°	164.5
67.5°	129.0
70°	96.1
72.5°	67.0
75°	41.8
77.5°	21.5
80°	7.6
82.5°	2.5
85°	1.2
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)