

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P205534

Luminaire Tested: **LSR6B40D010BZ EC6B30509730 6LBMGPH1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P205534  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LSR6B40D010BZ EC6B30509730 6LBMGPH1  
Description: PORTFOLIO 6IN CYLINDER  
MEDIUM DISTRIBUTION WITH GRAPHITE HAZE TRIM  
WATTAGE D010TR-43.02 W DE010-42.54 W D5LT-42.539 W DMX-41.87 W DL2-41.57  
W DL3-44.71 W DLE-39.33 W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1740.1 lumens  
Efficiency: N/A  
Efficacy: 41.6 lumens/watt  
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.91  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 41.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P205534

CATALOG NUMBER: LSR6B40D010BZ EC6B30509730 6LBMGPH1

### Luminous Intensity Polar Plot





TEST NUMBER: P205534

CATALOG NUMBER: LSR6B40D010BZ EC6B30509730 6LBMGPH1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									20																	
RC	80									70									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																					
RCR	0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100									100																										
	1	113	110	108	105	111	108	106	104	104	102	101	100	99	98	97	96	95	93																																			
	2	107	102	98	94	105	100	97	93	97	94	91	94	92	89	91	89	87	86																																			
	3	102	95	90	85	100	93	89	85	91	87	83	88	85	82	86	83	81	79																																			
	4	96	88	82	78	94	87	82	77	85	80	77	83	79	76	81	78	75	73																																			
	5	91	82	76	72	89	81	76	71	79	74	71	78	73	70	76	72	69	68																																			
	6	86	77	71	66	85	76	70	66	74	69	65	73	68	65	72	68	64	63																																			
	7	82	72	66	61	80	71	65	61	70	65	61	69	64	60	68	63	60	59																																			
	8	77	68	61	57	76	67	61	57	66	60	57	65	60	56	64	59	56	55																																			
	9	74	64	57	53	72	63	57	53	62	57	53	61	56	53	60	56	53	51																																			
	10	70	60	54	50	69	59	54	50	59	53	50	58	53	49	57	53	49	48																																			

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P205534

CATALOG NUMBER: LSR6B40D010BZ EC6B30509730 6LBMGPH1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	166.6	9.6
10°-20°	432.2	24.8
20°-30°	550.7	31.6
30°-40°	389.2	22.4
40°-50°	142.1	8.2
50°-60°	39.4	2.3
60°-70°	14.3	0.8
70°-80°	5.1	0.3
80°-90°	0.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1149.5	66.1
0°-40°	1538.7	88.4
0°-60°	1720.2	98.9
0°-90°	1740.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1740.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1813	
5°	1782	167
15°	1539	432
25°	1223	551
35°	618	389
45°	172	142
55°	42	39
65°	14	14
75°	4	5
85°	0	0
90°	0	



TEST NUMBER: P205534

CATALOG NUMBER: LSR6B40D010BZ EC6B30509730 6LBMGPH1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1813.2
2.5°	1806.2
5°	1781.6
7.5°	1732.4
10°	1679.7
12.5°	1609.4
15°	1539.1
17.5°	1468.9
20°	1398.6
22.5°	1314.2
25°	1222.9
27.5°	1096.4
30°	955.8
32.5°	787.1
35°	618.5
37.5°	470.9
40°	344.4
42.5°	249.5
45°	172.2
47.5°	116.0
50°	77.3
52.5°	52.7
55°	42.2
57.5°	31.6
60°	24.6
62.5°	17.6
65°	14.1
67.5°	10.5
70°	7.0
72.5°	7.0
75°	3.5
77.5°	3.5
80°	3.5
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)