

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P203273

Luminaire Tested: **LSR6B40D010BZ EC6B30509730 6LBMH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203273
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR6B40D010BZ EC6B30509730 6LBMH1
Description: PORTFOLIO 6IN CYLINDER
MEDIUM DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM
WATTAGE D010TR-43.02 W DE010-42.54 W D5LT-42.539 W DMX-41.87 W DL2-41.57
W DL3-44.71 W DLE-39.33 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2279.6 lumens
Efficiency: N/A
Efficacy: 54.5 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.93
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 41.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203273

CATALOG NUMBER: LSR6B40D010BZ EC6B30509730 6LBMH1

Luminous Intensity Polar Plot





TEST NUMBER: P203273

CATALOG NUMBER: LSR6B40D010BZ EC6B30509730 6LBMH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	92																			
2	107	102	97	93	105	100	96	92	97	93	90	94	91	88	91	89	87	85																			
3	101	94	88	84	99	92	87	84	90	86	82	87	84	81	85	82	80	78																			
4	95	87	81	76	93	86	80	76	84	79	75	82	78	74	80	76	73	72																			
5	90	81	75	70	88	80	74	70	78	73	69	76	72	68	75	71	68	66																			
6	85	75	69	64	83	75	69	64	73	68	64	72	67	63	70	66	63	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	76	66	60	55	75	65	59	55	64	59	55	63	58	55	62	58	54	53																			
9	72	62	56	51	71	61	55	51	60	55	51	60	55	51	59	54	51	49																			
10	69	58	52	48	68	58	52	48	57	52	48	56	51	48	55	51	48	46																			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203273

CATALOG NUMBER: LSR6B40D010BZ EC6B30509730 6LBMH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	206.3	9.0
10°-20°	533.6	23.4
20°-30°	691.4	30.3
30°-40°	513.3	22.5
40°-50°	216.7	9.5
50°-60°	77.0	3.4
60°-70°	29.7	1.3
70°-80°	10.3	0.5
80°-90°	1.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1431.3	62.8
0°-40°	1944.6	85.3
0°-60°	2238.2	98.2
0°-90°	2279.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2279.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2256	
5°	2207	206
15°	1904	534
25°	1533	691
35°	814	513
45°	267	217
55°	81	77
65°	29	30
75°	10	10
85°	0	1
90°	0	



TEST NUMBER: P203273

CATALOG NUMBER: LSR6B40D010BZ EC6B30509730 6LBMH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	2255.9
2.5°	2249.4
5°	2207.1
7.5°	2145.2
10°	2070.4
12.5°	1989.0
15°	1904.3
17.5°	1809.9
20°	1725.3
22.5°	1637.4
25°	1533.2
27.5°	1390.0
30°	1220.7
32.5°	1022.2
35°	813.8
37.5°	638.0
40°	485.0
42.5°	361.3
45°	266.9
47.5°	195.3
50°	143.2
52.5°	107.4
55°	81.4
57.5°	61.9
60°	48.8
62.5°	35.8
65°	29.3
67.5°	22.8
70°	16.3
72.5°	13.0
75°	9.8
77.5°	6.5
80°	3.3
82.5°	3.3
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)