

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P204370

Luminaire Tested: **LE_6B20D010 EC6B10208035 6LBSGPH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204370
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B20D010 EC6B10208035 6LBSGPH1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH GRAPHITE HAZE TRIM
WATTAGE D010TR-21.86 W DE010-20.46 W D5LT-21.24 W DMX-20.89 W DL2-22.5 W
DL3-21.8 6 W DLE-22.46 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2494.5 lumens
Efficiency: N/A
Efficacy: 119.9 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.26
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 20.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204370

CATALOG NUMBER: LE_6B20D010 EC6B10208035 6LBSGPH1

Luminous Intensity Polar Plot





TEST NUMBER: P204370

CATALOG NUMBER: LE_6B20D010 EC6B10208035 6LBSGPH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|---|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | | | | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | | | 0 | |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 |
| RCR | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | | | |
| 1 | 111 | 107 | 103 | 100 | 108 | 105 | 102 | 99 | 101 | 98 | 96 | 97 | 95 | 93 | 93 | 91 | 90 | 88 | | | |
| 2 | 102 | 95 | 89 | 84 | 100 | 93 | 88 | 83 | 90 | 85 | 82 | 87 | 83 | 80 | 84 | 81 | 78 | 76 | | | |
| 3 | 94 | 85 | 78 | 72 | 92 | 83 | 77 | 71 | 80 | 75 | 70 | 78 | 73 | 69 | 75 | 71 | 68 | 66 | | | |
| 4 | 87 | 76 | 68 | 62 | 85 | 75 | 67 | 62 | 72 | 66 | 61 | 70 | 65 | 60 | 68 | 63 | 59 | 57 | | | |
| 5 | 80 | 68 | 60 | 54 | 78 | 67 | 60 | 54 | 65 | 59 | 53 | 63 | 58 | 53 | 62 | 56 | 52 | 50 | | | |
| 6 | 74 | 62 | 54 | 48 | 73 | 61 | 53 | 48 | 59 | 52 | 47 | 58 | 52 | 47 | 56 | 51 | 47 | 45 | | | |
| 7 | 69 | 57 | 48 | 43 | 68 | 56 | 48 | 43 | 54 | 47 | 42 | 53 | 47 | 42 | 52 | 46 | 42 | 40 | | | |
| 8 | 65 | 52 | 44 | 38 | 63 | 51 | 44 | 38 | 50 | 43 | 38 | 49 | 42 | 38 | 48 | 42 | 38 | 36 | | | |
| 9 | 60 | 48 | 40 | 35 | 59 | 47 | 40 | 35 | 46 | 39 | 35 | 45 | 39 | 34 | 44 | 38 | 34 | 32 | | | |
| 10 | 57 | 44 | 37 | 32 | 56 | 44 | 36 | 32 | 43 | 36 | 31 | 42 | 36 | 31 | 41 | 35 | 31 | 30 | | | |

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204370

CATALOG NUMBER: LE_6B20D010 EC6B10208035 6LBSGPH1

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 109.1 | 4.4 |
| 10°-20° | 306.2 | 12.3 |
| 20°-30° | 446.6 | 17.9 |
| 30°-40° | 509.3 | 20.4 |
| 40°-50° | 488.5 | 19.6 |
| 50°-60° | 374.1 | 15.0 |
| 60°-70° | 205.3 | 8.2 |
| 70°-80° | 54.6 | 2.2 |
| 80°-90° | 0.8 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 861.9 | 34.6 |
| 0°-40° | 1371.1 | 55.0 |
| 0°-60° | 2233.8 | 89.5 |
| 0°-90° | 2494.5 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 2494.5 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|------|------|
| 0° | 1159 | |
| 5° | 1150 | 109 |
| 15° | 1087 | 306 |
| 25° | 970 | 447 |
| 35° | 814 | 509 |
| 45° | 635 | 489 |
| 55° | 419 | 374 |
| 65° | 207 | 205 |
| 75° | 48 | 55 |
| 85° | 0 | 1 |
| 90° | 0 | |



TEST NUMBER: P204370

CATALOG NUMBER: LE_6B20D010 EC6B10208035 6LBSGPH1

CANDELA DISTRIBUTION (FULL):

| | 0° |
|-------|--------|
| 0° | 1158.6 |
| 2.5° | 1155.6 |
| 5° | 1149.6 |
| 7.5° | 1140.6 |
| 10° | 1128.6 |
| 12.5° | 1107.6 |
| 15° | 1086.8 |
| 17.5° | 1062.8 |
| 20° | 1035.9 |
| 22.5° | 1002.9 |
| 25° | 970.0 |
| 27.5° | 937.0 |
| 30° | 895.1 |
| 32.5° | 856.2 |
| 35° | 814.2 |
| 37.5° | 772.4 |
| 40° | 730.5 |
| 42.5° | 685.6 |
| 45° | 634.6 |
| 47.5° | 583.8 |
| 50° | 529.9 |
| 52.5° | 473.0 |
| 55° | 419.1 |
| 57.5° | 365.2 |
| 60° | 308.4 |
| 62.5° | 254.5 |
| 65° | 206.6 |
| 67.5° | 158.6 |
| 70° | 116.8 |
| 72.5° | 77.9 |
| 75° | 47.9 |
| 77.5° | 21.0 |
| 80° | 6.0 |
| 82.5° | 0.0 |
| 85° | 0.0 |
| 87.5° | 0.0 |
| 90° | 0.0 |



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)